

Features


- Vitreous china.
- Elongated bowl.
- Include French Curve quiet close seat. (for K-30354X-C)
- Include polished chrome push button.
- Revolution 360 flushing system.
- Dual flush 3/4.8 liter per flush.
- 305 mm rough-in for S-trap.
- 700 x 398 x 782 mm

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 792-2554
- ASME A112.19.2/CSA B45.1

TWO-PIECE TOILET K-30354X-C, K-30354X-NS



Technical Information

Fixture:	
Configuration	Two-piece, Elongated
Water per flush	3/4.8 liter
Passageway	49 mm
Water area	192 x 146 mm
Water depth from rim	155 mm
Seat post hole centers	140 mm

Included Components:	
Bowl	K-30355X-**
Tank	K-23195X-**
Tank cover	1385301-SP-**
Quiet close seat (For K-30354X-C-**)	K-23204K-**
Toilet sealing washer	1626321-SP
Shut off valve, G1/2" x 1/2"	1552115-SP-**
Water supply hose, stainless	1548547-SP

Installation Notes


Install this product according to the installation guide.

Specified Model

Model	Description	Color/Finishes
K-30354X-C	Family Care Complete Solution, CS-trap with French Curve quiet close seat	0: White
K-30354X-NS	Family Care Complete Solution, CS-trap without seat	0: White


Dimensions are approximate. (Do not directly measure a dimension from picture below.)

Unit: mm



For ceramic connector installation

S-trap outlet
(P/N 1260287)




Note: The recommended dimension for installation can be adjusted according to user preferences and layout.
Kohler Co. reserves the right to make changes in product characteristics, packaging or availability at anytime without notice.

Product Diagram

สุขภัณฑ์สองชั้น

K-30354X-C, K-30354X-NS



คุณลักษณะ

- สุขภัณฑ์เซรามิกประภาวิเทรียสไชน่า (Vitreous china)
- โถสุขภัณฑ์แบบหน้ายาว
- พร้อมฝารองนั่งเฟรนช์เคิร์ฟแบบกันกระแทก (สำหรับ K-30354X-C)
- พร้อมปุ่มกดชำระสีโครมเงา
- ระบบชำระล้างเรโวลูชั่น 360
- ใช้น้ำในการชำระล้าง 3/4.8 ลิตร
- ระยะจุดกึ่งกลางท่อน้ำทิ้งถึงผนัง 305 มม. สำหรับการติดตั้งท่อน้ำทิ้งลงพื้น
- 700 x 398 x 782 มม.

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 792-2554
- ASME A112.19.2/CSA B45.1

ข้อมูลเฉพาะ

สุขภัณฑ์	
ลักษณะ	สุขภัณฑ์สองชั้น, หน้ายาว
การใช้น้ำชำระล้างต่อครั้ง	3/4.8 ลิตร
ขนาดท่อน้ำทิ้ง	49 มม.
ผิวหน้าน้ำ	192 x 146 มม.
ความลึกจากขอบโถสุขภัณฑ์ถึงผิวหน้าน้ำ	155 มม.
ระยะห่างระหว่างรูยึดฝารองนั่ง	140 มม.

ส่วนประกอบสุขภัณฑ์	
โถสุขภัณฑ์	K-30355X-**
ถังพักน้ำ	K-23195X-**
ฝาปิดถังพักน้ำ	1385301-SP-**
ฝารองนั่งแบบกันกระแทก (สำหรับ K-30354X-C-**)	K-23204K-**
ประเก็นกันกลิ่น	1626321-SP
วาล์ว เปิด-ปิด น้ำ, G1/2" x 1/2"	1552115-SP-**
สายน้ำดีสแตนเลส	1548547-SP


ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งสุขภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง


รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-30354X-C	สุขภัณฑ์สองชั้น แบบท่อลงพื้น รุ่น แฟมิลีแคร์ พร้อมฝารองนั่งเฟรนช์เคิร์ฟแบบกันกระแทก	0: สีขาว
K-30354X-NS	สุขภัณฑ์สองชั้น แบบท่อลงพื้น รุ่น แฟมิลีแคร์	0: สีขาว

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)
หน่วย: มม.



สำหรับการติดตั้งข้อต่อเซรามิก
ท่อน้ำทิ้งลงพื้น (P/N 1260287)



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง
บริษัทฯ ขอสงวนสิทธิ์ในการเปลี่ยนแปลงข้อมูลผลิตภัณฑ์ ปัจจุบันที่มีโดยมีต้องแจ้งให้ทราบล่วงหน้า

ภาพแสดงผลิตภัณฑ์