

安装说明

气动面板

记录您的型号:

Record your model number: _____

English, page 8

KOHLER®

1579785-T2-A

感谢您选择科勒


需要帮助？ 请联系我们的客户服务中心。

- 中国大陆：+(86) 800-820-2628, +(86) 400-820-2628
- 保养和清洁：kohler.com.cn/support/care-and-cleaning/

质保

本产品**在科勒®卫浴产品**的 3 年有效质保范围内，详见所附的《合格证》。

工具



开始之前


安装气动面板前，确保墙面施工已完成。

请遵守当地管路安装及建筑条例。

用锁紧螺栓和螺丝来安装固定框架。

对于面板的安装位置远离水箱的，请使用夹板安装固定框架。


1. 使用锁紧螺栓安装固定框架



注： 出厂时，面板与固定框架默认组装在一起。


- ☐ 如果墙面施工还没完成，请先施工完成墙面。
- ☐ 插入锁紧螺栓到固定框架。
- ☐ 将固定框架与水箱口对齐。
- ☐ 将锁紧螺栓转到“打开”位置。
- ☐ 如需要，请裁切锁紧螺栓，以便于墙壁平齐。
- ☐ 将锁紧螺栓转到“锁定”位置，以便将固定框架安装到位。

2. 使用螺丝安装固定框架（可选）



- 将固定框架与水箱口对齐。
- 拧紧螺丝，以便将固定框架安装到位。


3. 使用夹板安装固定框架（可选）



注： 对于面板的安装位置远离水箱的，请使用此安装方法。

- ☐ 如图所示，将夹板卡在墙。
- ☐ 将固定框架与水箱口对齐。
- ☐ 拧紧螺丝，以便将固定框架安装到位。

4. 连接气管




重要信息! 确认面板没有夹住气管。

注： 根据需要切割气管，避免气管弯折。

- ☐ 将用于大冲的（黑色）软管连接到大冲按钮背面的端口上。
- ☐ 将用于小冲的软管（蓝色）软连接到小冲按钮背面的端口上。

5. 固定面板



- ☐ 将面板向右旋转，使其紧贴墙壁。
- ☐ 用力按压面板两侧。
- ☐ 确认面板已卡入到正确位置。

Installation Instructions

Pneumatic Faceplate

Thank You for Choosing KOHLER


Need help? Contact our Customer Care Center.

- Mainland China: +(86) 800-820-2628, +(86) 400-820-2628
- **Care and cleaning:** kohler.com.cn/support/care-and-cleaning/

Warranty

This product is covered under the **Three-Year Limited Warranty for KOHLER® Plumbing Products**, found in the packed Compliance Certification.

Tools and Materials



Before You Begin


The finished wall must be in place before installing the pneumatic faceplate.

Follow all local plumbing and building codes.

The mounting frame can be installed with locking pins or screws.

For faceplate that are installed in a remote location from the in-wall tank, install the mounting frame with the clamps.


1. Install the Mounting Frame with Locking Pins



NOTE: The faceplate is assembled with the mounting frame by default.


- ☐ If not already installed, complete the finished wall at this time.
- ☐ Install the locking pins into the mounting frame.
- ☐ Align the mounting frame over the tank opening.
- ☐ Turn the locking pins to the "Open" position.
- ☐ If needed, cut the locking pins for a flush fit to the wall.
- ☐ Turn the locking pins to the "Lock" position to secure the mounting frame.

2. Install the Mounting Frame with Screws (Optional)



- ☐ Align the mounting frame over the tank opening.
- ☐ Tighten the screws to secure the mounting frame in position.


3. Install the Mounting Frame with Clamps (Optional)



NOTE: This installation option is applicable when the faceplate is to be installed at a remote location from the in-wall tank installed location.

- ☐ Position the clamps to the finished wall as illustrated.
- ☐ Align the mounting frame with the wall opening.
- ☐ Tighten the screws to secure the mounting frame in position.

4. Connect the Hoses




IMPORTANT! Verify that the hoses do not get pinched by the faceplate.

NOTE: Cut the hoses as needed, so that the hoses do not fold.

- ☐ Connect the full-flush hose (black) to the port on the back of the full flush button.
- ☐ Connect the half-flush hose (blue) to the port on the back of the half flush button.

5. Secure the Faceplate



- ☐ Turn the faceplate to the right toward the wall.
- ☐ Press firmly on both sides of the faceplate.
- ☐ Verify that the faceplate clicks into position.

kohler.com.cn

THE BOLD LOOK
OF **KOHLER**®

©2024 Kohler Co.



1579785-T2

1579785-T2-A