


34194T-S S-型去水弯管(E)



**订购时请说明颜色编号
**Color code must be specified when ordering

34194T-S S-型去水弯管(E)

安装之前

所有的资料是按最新出版的产品资料编写而成。科勒公司保留任何时候不经通知即可改变产品特性、包装或产品可供类型的权利。

说明书包括重要的安装、保养及清洁方面的内容，请把这些资料交给用户阅读。

注意事项:

- 1.遵守当地管路安装条例。
- 2.关闭主供水源。
- 3.如安装装饰罩：要求预置的地下排水管外径须为50mm，允许略高出装修好的地面，但不大于10mm。去水弯管伸入排水管长度不小于25mm。
- 4.如安装防反溢接头：要求预置的地下排水管外径须为50mm，且排水管高出地面至少35mm。

BEFORE YOU BEGIN

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.


Please leave these instructions for the consumer. They contain important information.

NOTES:

1. Observe all local plumbing codes.
2. Shut off the main water supply.
3. For installing escutcheon: Drain stub-out should be prearranged in the floor. Outside diameter of the drain stub-out must be Ø50mm. It can extend beyond the floor, but no more than 10mm. The pipe of the S-trap can reach into drain stub-out no less than 25mm.
4. For installing adapter: Drain stub-out should be prearranged in the floor. Outside diameter of the drain stub-out must be Ø50mm, and it can extend beyond the floor at least 35mm.

安装尺寸

ROUGH-IN DIMENSIONS



安装步骤

根据厂家的安装说明，安装排水组。

将去水弯管(4)上的连接螺帽(2)和垫圈(3)取下，依次将连接螺帽和垫圈套入排水组尾管(1)。手动旋紧连接螺帽。

注意： 确保落水头尾管插入连接螺帽长度不少于25mm。

如安装装饰罩： 要求预置的地下排水管外径须为50mm，允许略高出装修好的地面，但不大于10mm。去水弯管伸入排水管长度不小于25mm。




将去水弯管(4)上的连接螺帽(5)和垫圈(6)取下。将垫圈套入弯管(7)端头，依次将连接螺帽、装饰罩(8)和密封圈(9)从弯管出水口端套入。将弯管插入排水口(10)。调整两弯管的偏转角度，锁紧两连接螺帽以固定去水弯管。将密封圈塞入排水口，如弯管与排水口之间的间隙过小不能塞入密封圈，去掉密封圈，用密封胶填充间隙。将装饰罩下推与地面接触。

如安装防反溢接头： 要求预置的地下排水管(11)外径须为50mm，且排水管高出地面至少35mm。

将去水弯管(4)上的连接螺帽(5)和垫圈(6)取下。将垫圈套入弯管(7)端头，将连接螺帽(5)从弯管出水口端套入。调整两弯管的偏转角度，锁紧两连接螺帽以固定去水弯管。

依次将螺母(17)、垫圈(18)和垫圈(19)套入弯管(7)，将弯管(7)插入连接件(16)内，并用螺母(17)将其拧紧。

依次将螺母(12)、垫圈(13)和垫圈(14)套在排水管上，将排水内芯(15)插入排水管内，接着将连接件(16)安装到排水管上，并用螺母(12)将其拧紧。



INSTALLATION

Install the drain to lavatory according to the installation instruction.

Remove the nut(2) and washer(3) from the trap(4). Slide the nut and washer onto the tailpiece(1) of the drain. Then hand-tighten the nut.

NOTE: Ensure the tailpiece of the drain must be inserted into the nut no less than 25mm.

For installing escutcheon: Drain stub-out should be prearranged in the floor. Outside diameter of the drain stub-out must be Ø50mm. It can extend beyond the wall, but no more than 10mm. The pipe of the S-trap can reach into drain stub-out no less than 25mm.

Remove the nut(5) and washer(6) from the trap(4). Slide the washer onto the end of trap(7). Install the parts from outlet of trap according to the following order: the nut, escutcheon(8) and sealing ring(9). Insert the trap into drain stub-out(10). Adjust the angle of traps. Tighten the nuts to secure the traps. Push down the sealing ring into sub-out. If the gap between trap and sub-out is too small to push in the sealing ring, discard the sealing ring, fill the gap with sealants. Push escutcheon against the finished floor.

For installing adapter: Drain stub-out should be prearranged in the floor. Outside diameter of the drain stub-out (11) must be Ø50mm, and it can extend beyond the wall at least 35mm.

Remove the nut(5) and washer(6) from the trap(4). Slide the washer onto the end of trap(7). Install the nut(5) from outlet of the trap. Adjust the angle of traps. Tighten the nuts to secure the traps.

Slide the nut(17), gasket(18) and gasket (19) onto the trap(7) in sequence, insert the trap(7) into the joint(16), and tighten it with the nut(17).

Slide the nut(12), gasket(13) and gasket (14) onto the drain pipe in sequence, insert the drain core(15) into the drain pipe, and then install the joint(16) onto the drain pipe and tighten it with the nut(12).


安装结果检查

检查并确保所有的衔接螺帽都已拧紧。

打开排水器和主要供水源，检查并修理有漏水的接口。

清理去水弯管杂质

逆时针转动松开连接螺母(2、5)，取下弯管(4)，注意不要弄丢垫圈(3、6)。清理积在去水弯管(4)内的杂质，重新装回垫圈及弯管，锁紧螺母。



INSTALLATION CHECKOUT

Ensure all coupling nuts are tightened.

Turn on the drain and main water supply, check for leaks. Repair as needed.

Clean Debris in Trap

Turn the nuts(2, 5) connter-clockwise. Remove trap(4). Note: don't lose the washers(3, 6). Clean out any debris in the trap(4). Reinstall the washers and trap. Tighten the nuts.

清洗说明

适用于所有加工处理过的表面：以中性肥皂水清洗镀层表面，再以干净的软布彻底擦干整个表面，许多清洁剂，比如氨水、去污粉及洁厕灵等，会对电镀表面造成伤害，切忌使用。

有磨损性的清洁用具或清洁剂也不可使用于科勒牌的水龙头及其配件上。

CLEANING INSTRUCTIONS

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.