

### HYGIENE SPRAY K-29152T

#### Features

- Durable KOHLER finishes resist corrosion and tarnishing.
- Includes wall bracket and mounting fasteners suitable for various wall type.
- Multifunction hygiene spray provides two spray patterns.
  - Micro Bubble, gentle water flow for regular rinsing and cleaning.
  - Focused Spray, strong water flow for space cleaning in various situations and clean bathrooms.
- Easy to use button for switch spray patterns.
- Includes metal screen washer to prevent clogging.
- Includes 1.2 m PVC supply hose.



#### Codes/Standards Applicable

Specified model meets or exceeds the following:

- N/A


#### Installation Notes

Install this product according to the installation guide.


#### Specified Model

Model	Description	Color/Finishes	
K-29152T	Spacity hygiene spray	CP: Polished Chrome	Others

For a full range of color finishes in your market please contact your local Kohler representative.



**Flow Curve (Micro bubble spray)**




**Flow Curve (Focused spray)**

Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate. (Do not direct measure a dimensional from picture below.)

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

#### Product Diagram

### คุณลักษณะ

- วัสดุเคลือบผิวพิเศษจากโคห์เลอร์ คงทน เงางาม
- พร้อมขอแขวนซึ่งเหมาะสำหรับติดตั้งบนผนังทุกประเภท
- หัวฉีดชำระสามารถปรับเปลี่ยนสายน้ำได้ 2 รูปแบบ
  - ไมโครบับเบิลสเปร์ย์ สายน้ำแบบอ่อนโยนเพื่อการล้างและทำความสะอาดเป็นประจำ
  - ไฟกัสสเปร์ย์ สายน้ำแบบแรงดันสูงสำหรับการล้างทำความสะอาด
- ปุ่มปรับเปลี่ยนรูปแบบสายน้ำใช้งานง่าย
- พร้อมฟิลเตอร์เพื่อป้องกันการสะสมของตะกอน
- พร้อมสายน้ำดีแบบ พีวีซี ยาว 1.2 เมตร

### มาตรฐาน

คุณสมบัติตามมาตรฐาน

- ไม่ระบุ

### ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง



## สายฉีดชำระพร้อมสายอ่อนและขอแขวน K-29152T



### รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว	
K-29152T	สายฉีดชำระพร้อมสายอ่อนและขอแขวน รุ่นสเปซซีดี	CP: สีโครมเงา	อื่นๆ


ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศของท่าน



หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)

หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

### ภาพแสดงผลิตภัณฑ์