



Record your model number: \_\_\_\_\_

1625012-IN2

**CAUTION: Risk of product damage.** Do not use white cement or high lime-content cement to install this vitreous product. The expansion of cement due to rise in temperature may cause the product to crack or be damaged.

**IMPORTANT!** KOHLER Products work best with KOHLER accessories. Dry fit the accessories before installing the product to ensure fit. For recommended accessories, please visit [kohler.co.in](http://kohler.co.in) and reference the online product Specification Sheet.

Your product may appear different than the one illustrated. The installation procedure is the same.

Follow all local plumbing and building codes.

**READ AND FOLLOW ALL INSTRUCTIONS**

**SAVE THESE INSTRUCTIONS**

**1A.** Thread Sealant Tape

**1B.** Silicone Sealant

**1C.** Silicone Grease

**2A.** Install the inlet pipe gasket onto the inlet pipe. If needed, install the flow restrictor to the inlet pipe and wrap the flow restrictor with thread sealant tape before installing the gasket.

**3A.** Apply silicone grease where the brushes are shown.

**4A.** Install the inlet and outlet pipes to the toilet. Wipe away excess silicone grease.

**5A.** Mark the inlet and outlet pipes even with the back edge of the bowl.

**6A.** Remove the plaster guards before installing the inlet and outlet pipes.

**7A.** Mark the inlet and outlet pipes even with the front edge of the finished wall.

**8A.** Measure the distances "X" and "Y" between the marks and cut these lengths off the ends of the corresponding pipe.

**8B.** File the pipes to remove any burrs.

**9A.** Apply silicone grease.

**9B.** Apply silicone sealant.

**10A.** For -HC (Hidden Cord) Wall Hung Bowl: 1-9/16" (40 mm)

For non -HC (Hidden Cord) Wall Hung Bowl: 2-3/8" (60 mm)

**10B.** For -HC (Hidden Cord) and non -HC (Hidden Cord) Wall Hung Bowl: 3/8" (10 mm)

**11A.** Install the anchors and tighten using the provided tool.

**13A.** Use the provided 1/4" (6 mm) hex wrench to tighten the screws and secure the bowl.

**14A.** Apply silicone sealant.

**15A.** Wipe away any excess silicone sealant.

**Need help?** Contact our Customer Care Center.

• Email: [indiacustomer@kohler.com](mailto:indiacustomer@kohler.com)

• Call: 1800-103-2244

• **Care and cleaning:** Please refer to the Care and Cleaning on the product detail page.

This product is covered under the **KOHLER® India Sanitaryware and Bathing Products Limited Warranty**, found at [kohler.co.in/warranty](http://kohler.co.in/warranty). For a hardcopy of warranty terms, contact the Customer Care Center.



