


EX38214T-4 8寸脸盆龙头



**订购时请说明颜色编号
**Color code must be specified when ordering

EX38214T-4 8寸脸盆龙头

安装之前

所有的资料是按最新出版的产品资料编写而成。科勒公司保留任何时候不经通知即可改变产品特性、包装或产品可供类型的权利。

说明书包括重要的安装、保养及清洁方面的内容，请把这些资料交给用户阅读。

注意事项：

1. 一定要先彻底冲洗供水管以清除管道中的杂质。
2. 尽可能在安装脸盆之前安装水龙头。
3. 检查供水管有无损坏和漏水。如需要，进行替换和维修。
4. 遵守当地管路安装条例。
5. 切断供水管路。
6. 水嘴施加的水效标识表明本产品的水效等级等性能符合GB 25501-2019《水嘴水效限定值及水效等级》的要求，是产品符合性的一种标识。

BEFORE YOU BEGIN


All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice. Please leave these instructions for the consumer. They contain important information.



NOTES:




1. Flush the water supply pipes thoroughly to remove debris.
2. If possible, install this faucet before installing the lavatory.
3. Inspect the supply tubing for damage and leakage. Replace and maintain as necessary.
4. Observe local plumbing codes.
5. Shut off the water supplies to the fitting.
6. The water efficiency label applied to the faucet indicates that the water efficiency grade and other performance of the product meet the requirements of GB 25501-2019 "Minimum Allowable Values of Water Efficiency and Water Efficiency Grades for Faucets" which is a marking of product conformity.

安装尺寸

ROUGH-IN DIMENSIONS



安装步骤	INSTALLATION
	
如何安装出水口 将垫片(1)放入装饰盖(2)底部凹槽中，接着将出水口组件(3)插入脸盆安装孔中。 从脸盆下方将垫片(4)和螺母(5)装在固定螺栓(6)上。调整出水口的位置，锁紧螺母以固定出水口。 依次将塑料垫片(7)、橡胶垫圈(8)放入到T型接头(9)内，然后将T型接头旋到固定螺栓上并拧紧。 如何安装阀体和把手 先从阀体组件(10)上取下连接件(11)和橡胶垫片(12)。 确保垫片(13)、钢垫(14)和安装环(15)在阀体上。从脸盆下方将阀体组件装入脸盆安装孔(注：带红色标志的阀体组件装在左侧)。 将橡胶垫片(12)装到连接件底部凹槽中，将连接件装入阀体组件。 根据软管安装需要适当调整阀体出水口朝向。用螺丝刀拧紧螺钉(16)以固定阀体组件。 确保阀芯处于关闭状态。将把手组件(17)安装到连接件(11)上，在把手背后的螺钉孔中装入螺钉(18)并锁紧。注意：带有红色标记的把手组件装在左侧，带有蓝色标记的把手组件装在右侧。	How to Install the Spout Insert the washer(1) into the groove of the escutcheon(2) bottom. Install the spout kit(3) into the mounting hole of the lavatory. From underside of the lavatory, place the washer(4) and nut(5) onto the mounting stud(6). Position the faucet. Tighten the nut to secure the faucet. Put plastic washer(7) and rubber gasket washer(8) into supply tee(9). Thread supply tee to the mounting stud until tight. How to Install the Valve Bodies and Handles Remove the connector(11) and rubber washer(12) from each valve body(10). Be sure the washer(13), steel washer(14) and threaded ring(15) on the valve body. From the underside of the lavatory, install the valve body into the mounting hole of lavatory(NOTE: the valve body with red mark should be installed on the left side). Put the rubber washer(12) into the bottom groove of the connector. Tighten the connector onto the valve body. Adjust the outlets of side bodies to connect hoses easily. Secure the side bodies by tightening screws(16) with screwdriver. Ensure the valves are closed. Place the handle kits(17) onto the connector(11). Tighten the screw(18) from the backside of the handle. NOTE: The handle kit with red mark should be installed on the left side. The handle kit with blue mark should be installed on the right side.

如何连接软管 如图所示，用软管(19)将T型接头(9)与两边的阀体组件(10)侧面螺纹接口连接。		How to Connect the Hoses Connect the tee connector(9) to the side bodies(10) with hoses(19) as shown.
如何安装排水器 把锁紧螺母(20)、塑料垫片(21)、橡胶垫圈(22)和尾管(23)从排水本体(24)依次取下。在尾管螺纹处须缠绕足以密封的密封胶带或涂合适的密封胶，并装回排水本体。 把排水本体从脸盆上部孔插入。再依次将橡胶垫圈(小面朝上)、塑料垫片和锁紧螺母从脸盆下方装回到排水本体上。锁紧螺母。 注意：如果需要，可直接在法兰盘(25)底面沿周围涂一圈密封油灰或其它密封剂，而不使用橡胶垫片(26)。在锁紧螺母拧紧后，不可调整排水本体位置，否则会破坏油灰或密封剂密封。		How to Install the Drain Remove the locknut(20), plastic washer(21), rubber gasket(22) and tailpiece(23) from the drain body(24). Supply enough tape or sealant to tailpiece thread. Reinstall the tailpiece. Insert the drain body into the lavatory. Install the rubber gasket(Tapered side up), plastic washer and locknut back to the drain body in turn. Tighten the locknut. NOTE: If needed, apply a ring of plumbers putty or other sealants around the underside of the drain flange(25), instead of using rubber washer(26). Do not reposition the drain after the locknut is tightened, or you may break the putty or sealant seal.
安装结果检查 检查并确保所有衔接螺母都已拧紧，确保把手在关闭位置。打开排水器和主要供水源，检查是否有漏水。如有漏水，修理之。 用工具(27)拆下起泡器(28)。打开水龙头冷热水，让水流出约一分钟以清除杂质，检查渗漏。冲洗起泡器，关闭水龙头，重新装回起泡器。		INSTALLATION CHECKOUT Ensure all connections are tighten. Ensure the handle is in the off position. Turn on the drain and main water supply, and check for leaks. Repair as needed. Uninstall the aerator(28) with tool(27). Turn on the faucet. Run hot and cold water through the spout for about one minute to remove any debris. Check for leaks. Remove any debris from the aerator. Shut off the faucet. Reinstall the aerator.
使用说明 逆时针旋转右把手为开，顺时针旋转左把手为开。	HANDLE OPERATION Turn on the left handle clockwise is for hot water, turn on the right handle counter-clockwise is for cold water.	
清洗说明 适用于所有加工处理过的表面：以中性肥皂水清洗镀层表面，再以干净的软布彻底擦干整个表面，许多清洁剂，比如氨水、去污粉及洁厕灵等，会对电镀表面造成伤害，切忌使用。 有磨损性的清洁用具或清洁剂也不可使用于科勒牌的水龙头及其配件上。	CLEANING INSTRUCTIONS All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning. Do not use abrasive cleaners or solvents on Kohler faucets and fittings.	