



Underscore® Rectangle

66" x 32" drop-in VibrAcoustic® bath w/ Bask®
K-1822-VBW

Features

- VibrAcoustic calms and soothes with sound vibration technology.
- Six concealed speakers send sound waves through the water to gently massage the body.
- Six original instrumental compositions offer different levels of relaxation.
- Syncs with devices enabled with BLUETOOTH® wireless technology including smartphones, MP3 players, tablets, and laptops located up to 33 feet away.*
- Customize your experience with the high-resolution color touch screen.
- Fully-adjustable volume above and below the water.
- Functions as a hydrotherapy bath when full of water and a stereo system when empty.
- Bask® heated surface creates spa-like relaxation with soothing warmth on your back, shoulders, and neck.
- Three heat settings allow you to customize the surface temperature.
- Slotted overflow allows for deep soaking.
- Includes 25' of wiring and amplifier.

Material

- Acrylic.

Installation

- Drop-in or undermount.
- Requires 110 V electrical service.

Required Products/Accessories

- K-7271 Brass Slotted Overflow Bath Drain
or
K-7272 PVC Slotted Overflow Bath Drain

Recommended Products/Accessories

- 1184460 Undermount installation kit
K-1491 Bath/Whirlpool Pillow
K-1601 Bath/whirlpool footstop, removable
K-550 Under-Mount Installation Kit
K-1177 Vinyl Tiling-in Bead
K-23726 Drain treatment
K-23732 Tub & shower cleaner



Codes/Standards

CSA B45.11/IAPMO Z401
ASTM E162
ASTM E662
UL 1795

KOHLER® Plastic Baths and Receptors Lifetime Limited Warranty

See website for detailed warranty information.

The BLUETOOTH® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Kohler Co. is under license. Other trademarks and trade names are those of their respective owners.

Available Colors/Finishes


Color tiles intended for reference only.

Color	Code	Description
	0	White
	96	Biscuit
	NY	Dune
	95	Ice™ Grey
	G9	Sandbar
	K4	Cashmere
	58	Thunder™ Grey
	7	Black Black™




Underscore® Rectangle


66" x 32" drop-in VibrAcoustic® bath w/ Bask®
K-1822-VBW




No change in measurement if connected with drain illustrated. (K-7272)



Drop-In Rim Detail




User Interface



Amplifier

Control Access
30" (762 mm) W
x 15" (381 mm) H
Min



Required Electrical Service

One circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Amplifier, Heated 120 V, 15 A, 50/60 Hz
Surface:

Technical Information

All product dimensions are nominal.

Installation: Drop-in, Under-mount
Drain location: End
Basin area, bottom: 44-1/2" x 22-5/16" (1130 mm x 567 mm)
Basin area, top: 59-5/8" x 25-1/2" (1514 mm x 648 mm)
Weight: 96 lbs (43.5 kg)
Minimum floor load: 58 lbs/ft² (283.2 kg/m²)
Water depth: 18" (457 mm)
Water capacity: 85 gal (321.8 L)
Cutout: Drop-in, 64-1/2" x 30-1/2" (1638 mm x 775 mm)
Electrical component rating: Amplifier: 120 V, 50/60 Hz
Heated Surface: 120 V, 0.5 A, 50/60 Hz, 65 W

Bluetooth® range: 33 ft (0.8 m)

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com.

5-16-2021 04:42 - US/CA

Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Kit is required for under-mount installations (sold separately).

Control amplifier fits 16" (406 mm) center studs. 25' (7.6 m) cables are included.

IMPORTANT! Due to BLUETOOTH signal overlap, installations of multiple baths within 50 ft (15.2 m) of each other will require special order product. Please contact your dealer, showroom, or sales representative for ordering assistance.

THE BOLD LOOK
OF **KOHLER**®