

Features


- *Vitreous china*
- *Semi-pedestal lavatory*
- *Available in single-hole or 8" centers*
- *With overflow*
- *572 x 454 x 410 mm*

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2/CSA B45.1
- TIS 791-2544

SEMI-PEDESTAL LAVATORY
K-18564X/K-18566X



Technical Information

Fixture:	
Basin area	400 x 304 mm
Water depth	135 mm
Drain hole	44 mm D.
*Approximate measurements for comparison only.	

*Approximate measurements for comparison only.

Included Components:	
Basin, single-hole	K-18564X-1
Basin, 8" centers	K-18564X-8
Semi-pedestal	K-18566X
Wall mounted fixing pack	1049141
Hardware pack	1249336

Installation Notes

Install this product according to the installation guide.

Specified Model

Model	Description	Color/Finished
K-18564X-1	Reach basin, single-hole	0: White
K-18564X-8	Reach basin, 8" centers	0: White
K-18566X	Reach semi-pedestal	0: White


Recommended Accessories

K-7119T	Click drain	CP: Polished chrome
K-9071T	Bottle-trap	CP: Polished chrome



Dimensions are approximate.

Unit: mm

K-18564X-1



K-18564X-8



Product Diagram

คุณลักษณะ


- สุขภัณฑ์เซรามิกประเภทวิเทรียสไชน่า (Vitreous china)
- ติดตั้งแบบแขวนพร้อมขาของอ่างแบบแขวน
- แบบเจาะรูเดี่ยว หรือแบบเจาะเซ็นเตอร์ 8"
- พร้อมม้วนน้ำล้น
- 572 x 454 x 410 มม.

มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- ASME A112.19.2/CSA B45.1
- มอก. 791-2544

อ่างล้างหน้าแบบแขวน พร้อมขาของอ่างแบบแขวน

K-18564X/K18566X



ข้อมูลเฉพาะ

สุขภัณฑ์	
พื้นที่ใช้งานในอ่างล้างหน้า	400 x 304 มม.
ระยะน้ำล้น	135 มม.
ขนาดรูสะดืออ่าง	เส้นผ่าศูนย์กลาง 44 มม.
*ขนาดระยะโดยค่าประมาณเพื่อการเปรียบเทียบเท่านั้น	

ส่วนประกอบผลิตภัณฑ์	
อ่างล้างหน้า แบบเจาะรูเดี่ยว	K-18564X-1
อ่างล้างหน้า แบบเซ็นเตอร์ 8"	K-18564X-8
ขาของอ่างแบบแขวน	K-18566X
ชุดอุปกรณ์ยึดอ่างล้างหน้า	1049141
ชุดอุปกรณ์ยึดขาอ่างล้างหน้า	1249336

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-18564X-1	อ่างล้างหน้า แบบเจาะรูเดี่ยว รุ่น รีช	0: สีขาว
K-18564X-8	อ่างล้างหน้า แบบเซ็นเตอร์ 8" รุ่น รีช	0: สีขาว
K-18566X	ขาของอ่างแบบแขวน รุ่น รีช	0: สีขาว

ข้อสังเกตสำหรับการติดตั้ง


ติดตั้งสุขภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

อุปกรณ์แนะนำ		
K-7119T	สะดืออ่างล้างหน้าแบบกด	CP: สีโครมเงา
K-9071T	ท่อน้ำทิ้งอ่างล้างหน้าแบบกระบอก	CP: สีโครมเงา



ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.

K-18564X-1



K-18564X-8



ภาพแสดงผลิตภัณฑ์