



Underscore® Cube

48" x 48" drop-in VibrAcoustic® bath w/chromatherapy
K-1969-VBC

Features

- VibrAcoustic calms and soothes with sound vibration technology.
- Six concealed speakers send sound waves through the water to gently massage the body.
- Six original instrumental compositions offer different levels of relaxation.
- Syncs with devices enabled with BLUETOOTH® wireless technology including smartphones, MP3 players, tablets, and laptops located up to 33 feet away.*
- Customize your experience with the high-resolution color touch screen.
- Fully-adjustable volume above and below the water.
- Functions as a hydrotherapy bath when full of water and a stereo system when empty.
- Chromatherapy lighting allows you to select a preferred color scheme to suit your mood.
- Spacious design accommodates up to two bathers.
- Two integral corner seats at different heights.
- Extra-deep bathing well for added comfort.
- Slotted overflow allows for deep soaking.
- Includes 25' of wiring and amplifier.

Material

- Acrylic.

Hydrotherapy

- Chromatherapy.

Installation

- Drop-in or undermount.
- Requires 110 V electrical service.

Recommended Products/Accessories

1184460 Undermount installation kit
K-578 Cube Undermount Installation Kit
K-8134 Cable Bath Drain Trim Kit
K-8150 Cube Cable Drain
K-1177 Vinyl Tiling-in Bead
K-23726 Drain treatment
K-23732 Tub & shower cleaner



Codes/Standards

ASME A112.19.7/CSA B45.10
CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662
UL 1795
CSA C22.2 No. 218.2

KOHLER® Plastic Baths and Receptors Lifetime Limited Warranty
See website for detailed warranty information.





The BLUETOOTH® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Kohler Co. is under license. Other trademarks and trade names are those of their respective owners.




Underscore® Cube

48" x 48" drop-in VibrAcoustic® bath w/chromatherapy
K-1969-VBC

No change in measurements if connected with drain illustrated. (K-8150)



*Recommended User Interface Location



Required Electrical Service

One circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Amplifier: 120 V, 15 A, 50/60 Hz

Technical Information

All product dimensions are nominal.

Installation: Drop-in, Under-mount

Drain location: Center

Basin area, bottom: 39-3/8" x 39-3/8" (1000 mm x 1000 mm)

Basin area, top: 44-5/8" x 44-5/8" (1133 mm x 1133 mm)

Weight: 115 lbs (52.2 kg)

Minimum floor load: 99 lbs/ft² (483.4 kg/m²)

Water depth: 27-1/2" (699 mm)

Water capacity: 171 gal (647.3 L)

Cutout: Drop-in, 47" x 47" (1194 mm x 1194 mm)

Electrical component rating: Amplifier: 120 V, 1.1 A, 50/60 Hz

Amplifier channels: 2 at 15 W per channel
2 at 30 W per channel

Bluetooth® range: 33 ft (10.1 m)

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com.

5-15-2021 18:00 - US/CA/MX

Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Kit is required for under-mount installations (sold separately).

Control amplifier fits 16" (406 mm) center studs. 25' (7.6 m) cables are included.

IMPORTANT! Due to BLUETOOTH signal overlap, installations of multiple baths within 50 ft (15.2 m) of each other will require special order product. Please contact your dealer, showroom, or sales representative for ordering assistance.

THE BOLD LOOK
OF **KOHLER**