

### Features

- Vitreous China
- Symmetrical Design
- Without Overflow
- Rim Above counter



### Recommended Accessories

- Ceramic Drain (24740IN)
- Bottle Trap (75823IN)

COMPATIBLE FAUCETS	
PRODUCT DESCRIPTION	SKU CODE
ALEO LAV FAUCET W/O DRAIN	72275IN-4ND-CP
ALEO + SINGLE-CONTROL LAVATORY FAUCET	72312IN-4-CP
AVID LAV FAUCET WITH DRAIN	97345IN-4-CP
CABRIOLE SINGLE CONTROL LAVATORY FAUCET WITH LEVER HANDLE WITHOUT DRAIN	K-8600IN-1ND-CP
CANDIDE SINGLE CONTROL LAVATORY FAUCET WITH LEVER HANDLE WITHOUT DRAIN	K-660IN-ND-CP
COMPOSED SC SIDE MOUNT LAV FAUCET W/D	73050IN-7-CP
CUFF SINGLE CONTROL LAVATORY FAUCET W/O DRAIN	K-37301IN-4ND-CP
EOLIA SINGLE CONTROL LAVATORY FAUCET WITH LEVER HANDLE WITHOUT DRAIN	K-8620IN-ND-CP
FAIRFAX SINGLE LEVER LAV FAUCET	8657IN-CP
HINT™ SC LAV FAUCET W DRAIN	97060IN-4-CP
JULY SINGLE CONTROL LAVATORY FAUCET WITH LEVER HANDLE WITHOUT DRAIN	K-16027IN-4ND-CP
KUMIN SC LAV FAUCET WITH DRAIN	98827IN-4-CP
LOURE SINGLE CONTROL LAV FAUCET	10319IN-4-CP
MARGAUX LAVATORY SINGLE CONTROL FAUCET	16230IN-4-CP
NATEO MONOBLOCKSGL CONTROL LAV FAUCET	K-18000IN-ND-CP
PURIST SINGLE CONTROL LAVATORY FAUCET WITHOUT DRAIN	K-14402IN-4ND-CP
QUALIS SC LAV WITHOUT DRAIN	13523IN-4ND-CP
SINGULIER LAV FAUCET WITH DRAIN	10860IN-4-AF
SIROCCO DUAL HANDLE LAVATORY FAUCET	8611IN-7ND-CP
STANCE SC LAVATORY FAUCET	14760IN-4ND-CP
STRAYT PILLAR TAP	K-37333IN-4-CP
SYMBOL SINGLE CONTROL LAVATORY FAUCET	19480IN-CP
TAUT™ SC LAV FAUCET WITH DRAIN	74013IN-4-CP
VITEO SINGLE CONTROL LAVATORY FAUCET WITH LEVER HANDLE WITHOUT DRAIN	K-5695IN-4ND-CP
WAVE SINGLE CONTROL LAVATORY FAUCET WITH LEVER HANDLE & POP-UP DRAIN	K-9076IN-CP


### KOHLER® Ten-Year Limited Warranty

See website for detailed warranty information.

### Available Color/ Finishes

Color tiles intended for reference only

Color	Code	Description
■	0	White



### Notes

Install this product according to the installation instructions.

Product does not have an overflow.

\*Spout must be 3.9" (99mm) long (min) for adequate clearance into the bathroom sink.

NOTICE: Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler (1800-103-2244). Kohler is not responsible for cutout errors when incorrect cut-out template is used.

### Technical Information

All Product Dimensions are nominal

Vessel configuration	Self Rimming with Deck
Installation	Above counter
Bowl area	Length: 16 1/4" (413 mm) Width: 18 1/8" (460mm) Height: 1 3/8" (35mm) Depth: 5" (127mm)
Drain hole	Ø41.65 - 46.5 mm
Installation Template	1302582-K7