


- 31878T-4 Wall-Mount Shower Faucet Streamline Handle with Bracket 6P
- 31880T-4 Wall-Mount Shower Faucet Streamline Handle without Bracket 6P
- 31877T-4 Wall-Mount Bath Shower Faucet Streamline Handle with Bracket 6P
- 31879T-4 Wall-Mount Bath Shower Faucet Streamline Handle without Bracket 6P



**Color code must be specified when ordering

- 31878T-4 Wall-Mount Shower Faucet Streamline Handle with Bracket 6P
- 31880T-4 Wall-Mount Shower Faucet Streamline Handle without Bracket 6P
- 31877T-4 Wall-Mount Bath Shower Faucet Streamline Handle with Bracket 6P
- 31879T-4 Wall-Mount Bath Shower Faucet Streamline Handle without Bracket 6P

BEFORE YOU BEGIN

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.


Please leave these instructions for the consumer. They contain important information.

- NOTES:**
- 1. Observe local plumbing codes. Inspect the supply tubing for damage. Replace if necessary.
 - 2. The minimum inlet water pressure for diverter is 0.05MPa(0.5bar).
 - 3. The highest working pressure for handshower & showerhead is 0.5MPa(5bar). If it exceeds 0.5MPa(5bar), a pressure reducer is needed. The highest water and environment temperature is 60°C. Please keep handshower, showerhead and shower arm away from heater, or it may become damaged and cause injury to the user.

HANDLE OPERATION

Lift the handle gently. Turn clockwise for hot water, turn counter-clockwise for cold water. For 31877T & 31879T, water flows out from spout when faucet diverter is in the normal position; Lift the diverter gently, turn clockwise for handshower; Shut off the faucet, turn counter-clockwise until it stops.


ROUGH-IN DIMENSIONS



INSTALLATION


How to Install the Faucet

To perform installation, installer must provide G1/2" female supply fittings(1), spaced 150mm apart and horizontally. The supply fittings should be vertical and not beyond the finished wall. Hot supply pipe must be located on the left.




Flush the water supply pipes thoroughly to remove debris.

Use appropriate thread sealants on threads of offset connectors. Install two offset connectors(2) into the HOT and COLD supply pipes.



Adjust the center-to-center distance between the connectors to 150mm horizontally. They should extend 26mm beyond the finished wall.

Thread the escutcheons(3) onto the connectors until they are against the finished wall. Put the washers(5) into the nuts(4) of the faucet. Thread the nuts to the connectors.




NOTE: When tighten the nuts, use strap wrench or soft cloth between product and regular wrench to protect the finish.

Insert the regulator(9) into the handshower(10) if needed. Put the washers(6) into the hose(8). Connect the faucet outlet(7) and handshower with hose.

How to Install the Bracket (Only for 31878T & 31877T)

Determine a suitable location on the finished wall to install the bracket. Mark bracket mounting hole locations on the wall according to the dimension. Drill two holes on the finished wall, the holes should match the anchors(11). Install the anchors.



Tighten screws(12) to secure bracket(13, flat side upward) until it against the finished wall.


INSTALLATION CHECKOUT

Ensure all connections are tight.

Ensure the handle is in the off position.

Turn on the main water supply, and check for leaks. Repair as needed.

Remove the aerator(14) with coin. Remove the handshower(10). Run hot and cold water through the faucet for about one minute to remove any debris. Check for leaks. Remove any debris from the aerator. Shut the faucet off, and reinstall the aerator and handshower.



CLEANING INSTRUCTIONS

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.