



* Color code must be specified when ordering.
* 订购时请说明颜色编号。

P/N 零件号	DESCRIPTION 描述		COLOR颜色	
★ 1343895-R*	Door Glass, RH, New Purist, 10mm 门玻璃 (右开) 10mm		FM, IC	
★ 1344040-R*	Panel Glass, Seal, RH, New Purist, 10mm 密封房铰链固玻 (右开) 10mm			
★ 1343895-L*	Door Glass, LH, New Purist, 10mm 门玻璃 (左开) 10mm			
★ 1344040-L*	Panel Glass, Seal, LH, New Purist, 10mm 密封房铰链固玻 (左开) 10mm			
★ 1344042*	Skylight Glass, Seal, New Purist 密封房天窗玻璃			
★ 1343898*	Wall Channel Clamp, New Purist 新飘瑞诗上墙材		2BL, SHP	
★ 1343906*	Wall Jamb Clamp, New Purist 新飘瑞诗夹材		2BL, SHP	
★ 1343908*	Wall Jamb Clamp Cap, New Purist 新飘瑞诗夹材装饰材		2BL, SHP	
★ 1344041-R*	Side Frame, RH, New Purist 新飘瑞诗边立柱 (右开)		2BL, SHP	
★ 1344041-L*	Side Frame, LH, New Purist 新飘瑞诗边立柱 (左开)		2BL, SHP	
★ 1344043*	Top Rail Frame, New Purist 新飘瑞诗密封房顶横梁		2BL, SHP	
★ 1341594-R*	Bottom Frame, RH, New Purist 新飘瑞诗底横梁 (右开)		2BL, SHP	
★ 1341594-L*	Bottom Frame, LH, New Purist 新飘瑞诗底横梁 (左开)		2BL, SHP	
1325088-R*	Hinge Assy, Up, RH, New Purist 新飘瑞诗上铰链组件 (右开)		2BL, S, RGD, AF, BN, BV	
1325149-R*	Hinge Assy, Bottom, RH, New Purist 新飘瑞诗下铰链组件 (右开)		2BL, S, RGD, AF, BN, BV	
1325088-L*	Hinge Assy, Up, LH, New Purist 新飘瑞诗上铰链组件 (左开)		2BL, S, RGD, AF, BN, BV	
1325149-L*	Hinge Assy, Bottom, LH, New Purist 新飘瑞诗下铰链组件 (左开)		2BL, S, RGD, AF, BN, BV	
1210221-*	Purist Transom Pivot Assy, 1D1P 飘瑞诗一固一活天窗转轴组件		2BL, S, RGD, AF, BN, BV	
1210215-*	Purist Transom Pivot Assy, 1D2P 飘瑞诗两固一活天窗转轴组件		2BL, S, RGD, AF, BN, BV	
★ 1272963*	Composed Handle Assy, 450mm, Double 对装柏诗拉手 450mm		2BL, S, RGD, AF, BN, BV	
★▲ 1344065	New Purist Pivot Seal Strip Package Kit, 10mm, 新飘瑞诗开门密封配件包, 密封房 10mm	1343931	Insert Magnetic Seal, 10mm, Skyline 铝材磁条 10mm	
		1343932	Magnetic Seal, 180°, 10mm, 180度门吸磁条 10mm	
		1343940	Magnetic Seal, Inward Opening, 10mm 内开磁条 10mm	
		1343929	Bottom Seal For Purist DR Glass Profile 门底胶条	
		1343930	Side Seal, 10mm, Profile, Hinged Door 侧边胶条 10mm	
		1343952	Side Seal, Inner Open, New Purist, 10mm 内开门侧边胶条	
		1343933	Glass Gripping Seal, Profile, 10mm 固玻压紧胶条 10mm	
		1343934	Inserted Seal For Bottom Frame 底横梁嵌入胶条	
		1341685	Wall Side Seal, 10mm, Profile 泡泡胶条 10mm	
		1210250	Cover Seal 装饰胶条	
1157883	Insert Seal 单边胶条			
★▲ 1344066	New Purist Pivot SP Package Kit, 新飘瑞诗开门维修配件包密封房	1272936	Connector Block 塑胶压块	
		1210861	Screw ST3.5X6 非尖头螺丝 (锁塑胶压块用) ST3.5X6	
		1343936	Screw M4X8 十字沉头机制螺钉M4X8	
		1343947	Screw M5X8 平头顶丝M5X8	
		1150121	Screw, GB/T 845 ST3.5X40 盘头十字自攻螺钉 ST3.5X40	
		1057064	Wall Anchor 膨胀套 (入墙胶粒)	
		1157853	Screw Key 2.5mm 内六角扳手 2.5mm	
		1095457	Screw Key 3mm 内六角扳手 3mm	
		1078917	Screw Key 4mm 内六角扳手 4mm	
		1178609	Screw Key 5mm 内六角扳手 5mm	

Note: Components marked in ▲ can only be ordered in whole pack. When ordering components marked in ★, customers need provide measurement form and corresponding product SKU.

注意: 带▲标注零件仅可整包订购, 带★标注零件订购时需附加测量单和产品SKU号。

Glass options: C

玻璃花纹可供选择: C

FM-It is for filmed glass. The following decorative patterns can be chosen (refer to the table below) together with FM glass.

IC-It is for laminated glass with easy clean coating. The following decorative patterns cannot be chosen together with IC glass.

FM- 此号码为防爆膜玻璃, 配备FM时, 可以选择以下指定花纹代码 (参考下表)。

IC- 此号码为夹层+超净玻璃, 配备IC时, 以下代码不能再选择。

Refer to the table below for glass options

玻璃选项参考下表

P/N 零件号	DESCRIPTION 描述
1291888-L1	蕾丝花纹, L1
1291888-L3	思绪花纹, L3
1291888-L4	梅玛花纹, L4
1291888-L5	晨雾花纹, L5
1291888-L8	繁星花纹, L8
1291888-L9	丝雨花纹, L9
1291888-MZ	镜面玻璃, MZ
1291888-CI	镜面繁星花纹, CI
1291888-EL	镜面银河花纹, EL
1291888-GB	金色夏宫花纹, GB
1291888-C	超净玻璃, C