



# Forum™ Traverse®

60" x 36" Vikrell bath/shower with AIP backerboards,  
grab bars, & bath seat, right drain  
**71620125**



## Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Modern subway tile design
- Full-length shelf provides generous storage
- Factory-installed Aging in Place backerboards for future grab bar installation
- Five-piece grab bar kit
- 16" x 22" (406 x 559 mm) bath seat with telescoping legs and non-slip feet clamps securely to bath
- Innovative Dry-Block™ seal and channeled water containment system form watertight seams

## Material

- Compression-molded from our exclusive solid Vikrell® material

## Installation

- Pro4™ installation system features a two-piece back wall design, enabling one-person handling and installation
- Alcove
- Right drain
- Caulk-free installation

## Included Components

- 71504106 60" x 36" Vikrell® bath/shower wall set with Aging in Place backerboards
- 71577103 5-Piece ADA-adaptable grab bar kit
- 71607104 16" x 22" bath seat
- 71621120 60" x 36" Vikrell® alcove bath, right drain



**ADA**

## Codes/Standards

CSA B45.5/IAPMO Z124  
ASTM E162  
ASTM E662  
ADA  
ICC/ANSI A117.1

## STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

### Color Code Description


|                                                                                     |   |       |
|-------------------------------------------------------------------------------------|---|-------|
|  | 0 | White |
|-------------------------------------------------------------------------------------|---|-------|

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.sterlingplumbing.com](http://www.sterlingplumbing.com).

12-7-2025 20:30 - US



### Technical Information

All product dimensions are nominal.

|                        |                   |
|------------------------|-------------------|
| Drain location:        | Right             |
| Weight:                | 170 lbs (77.1 kg) |
| Water depth:           | 13-1/4" (337 mm)  |
| Water capacity:        | 61 gal (230.9 L)  |
| Minimum flat for door: | 3" (76 mm)        |
| Maximum door height:   | 56-3/4" (1441 mm) |
| Maximum door width:    | 57-5/8" (1464 mm) |

### Notes

Install this product according to the installation instructions.

ADA compliant when installed to the specific requirements of these regulations.