


安装步骤


如何安装T型接头

将垫片(2)放入T型接头(4)的螺母(3)内后, 将T型接头(4)接到用户所选配浴缸龙头的一侧阀体(1)上, 如图所示。



如何安装切换阀体


从切换器上依次拆下棘齿圈(5)、装饰盖(6)和垫片(7)。将带有垫片(8)和螺母(9)的切换器组件(10)从台面的下方插入安装孔。从上方依次装上垫片(7)、装饰盖(6)、棘齿圈(5)。拧紧装饰盖, 然后用扳手锁紧螺母(9)。



将把手(11)向下压入阀体。


如何安装花洒

拆下螺母(15)、垫片(14), 将橡胶垫片(13)置于装饰盖(12)的底面凹槽内。将牙管插入安装孔。从下方将垫片(14)、螺母(15)安装到牙管上, 拧紧螺母。



将软管(20)(长2m)穿过导向套(21)连接到软管(22)(长0.6m)上。

将垫片(17)放入弯头组件(18), 把弯头组件旋接到花洒(16)上。用垫片(19)连接软管及弯头组件。



INSTALLATION

How To Install The Tee

Put the washer(2) into the nut(3) of the tee(4). Then connect the tee(4) to one side body(1) of the deck-mount bath faucet as the figure shown.

How To Install Diverter Body

Remove the parts from the diverter body according to the following order: ratchet ring(5), escutcheon(6) and washer(7). Insert the diverter body(10) with washer(8) and nut(9) through mounting hole from underside of the deck. Reinstall the parts according to the following order: washer(7), escutcheon(6) and ratchet ring(5). Tighten the escutcheon, then wrench tighten the nut(9).

Press the handle(11) to the diverter body.

How To Install The Handspray

Remove the nut(15), washer(14). Put the rubber washer(13) into the groove of the escutcheon(12). Place the shank into the hole. From underside, install the washer(14) and nut(15) to the shank. Then tighten the nut firmly.

Slide the hose(20)(length: 2m) through the hose guide(21), and attach to the hose(22)(length: 0.6m).

Put the washer(17) into the elbow assembly(18), and then thread them to handspray(16). Connect the hose and the elbow assembly with the washer (19).

把垫片(23)放入螺母(24), 并将其旋到所选配浴缸出水口的T型接头(25)的任意端口上锁紧。

Put the fiber washer(23) into the plug(24), Tighten the plug to one of the ports of the center tee(25) for the spout.

用垫片及随浴缸龙头附带的一根软管(龙头附带的另一软管去掉不用)连接一侧阀体(29)和另一侧阀体的T型接头(4)。用软管(28)(长1m)及垫片连接T型接头(4)和切换器底部接口。用垫片连接软管(26)及切换器花洒接口(贴有提示签的一端)。用软管(27)(长1m)及垫片连接出水口T型接头(25)和切换器的另一出水口。

Connect one side body(29) and the tee(4) on another side body with washers and one of the hoses provided with the deck-mount faucet(Remove another hose and put it away). Connect the tee(4) and bottom port of the diverter with hose(28)(length:1m) and washers. Tighten the connection hose(26) to the end(with note label) with washer. Connect the center tee(25) and another end of the diverter with hose(27) (length:1m) and washers.

为保证水流顺畅, 花洒抽取自如, 应该避免软管打结、缠绕。为了安装方便, 可以适当旋松出水口的T型接头, 但不要超过180°。

To ensure the water flows smoothly and the hand-spray can be drawn out easily, the hose should avoid kinking, twisting. To ease installation, you may back off center tee of the spout up to 180 degree.

注意: 软管只能用于指定部位。

Note: Hoses should only be used where indicated.

安装结果检查

确保所有连接螺母都已拧紧。打开主供水源, 检查并修理有漏水的接口。

清理说明

适用于所有加工处理过的表面: 以中性肥皂水清洗镀层表面, 再以干净的软布彻底擦干整个表面, 许多清洁剂, 比如氨水、去污粉及洁厕灵等, 会对电镀表面造成伤害, 切忌使用。

有磨损性的清洁用具或清洁剂也不可适用于科勒牌的水龙头及其配件上。

INSTALLATION CHECKOUT

Ensure all coupling nuts are tight. Turn on main water supply and check for leaks. Repair as required.

CLEANING INSTRUCTIONS

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.