


73081T-B9ACH 双把缸边式浴缸龙头-琥珀金琉璃把手

73081T-B9GCH 双把缸边式浴缸龙头-水墨灰琉璃把手



****订购时请说明颜色编号**

**Color code must be specified when ordering

73081T-B9ACH 双把缸边式浴缸龙头-琥珀金琉璃把手

73081T-B9GCH 双把缸边式浴缸龙头-水墨灰琉璃把手

安装之前

所有的资料是按最新出版的产品资料编写而成。科勒公司保留任何时候不经通知即可改变产品特性、包装或产品可供类型的权利。

说明书包括重要的安装、保养及清洁方面的内容，请把这些资料交给用户阅读。


注意事项:

1. 一定要先彻底冲洗供水管以清除管道中的杂质。
2. 检查供水管有无损坏和漏水。如需要, 进行替换和维修。
3. 遵守当地管路安装条例。
4. 切断主供水源。尽可能在安装浴缸前安装水龙头。
5. 禁止用60°C以上的热水浇把手, 否则可能导致把手开裂。
6. 禁止用硬物撞击把手, 否则可能导致把手开裂。
7. 禁止用酒精等有机溶剂擦拭把手。

使用说明

逆时针旋转右把手为开，顺时针旋转左把手为开。

安装尺寸



BEFORE YOU BEGIN

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.

Please leave these instructions for the consumer.
They contain important information.

NOTES:

1. Flush the water supply pipes thoroughly to remove debris.
2. Inspect the supply tubing for damage and leakage. Replace and maintain as necessary.
3. Observe local plumbing codes.
4. Shut off the water supplies to the fitting. If possible, install this faucet before installing the tub.
5. Do not pour hot water above 60°C into the handle, or it may become cracking.
6. Do not hit the handle with hard objects, or it may become cracking.
7. Do not use alcohol and other organic solvents to wipe the handle.

HANDLE OPERATION

Turn on the left handle clockwise is for hot water, turn on the right handle counter-clockwise is for cold water.

ROUGH-IN DIMENSIONS

安装步骤

INSTALLATION

如何安装出水口

将T型接头(6)、螺母(4, 5)和垫片(3)从牙管(1)上拆下来。

将牙管带垫片(2)插入台面安装孔中，从台面下方套上垫片(3)，拧紧螺母(4, 5)固定牙管。


将T型接头(6)用手旋紧到牙管上。

取下出水口背部的塞扣(12)和O型圈(11)，用扳手(9)旋松螺钉(10)。

将装饰盖(7)装在牙管上，贴紧台面。

然后将出水口(8)套在牙管上贴紧装饰盖。调整好出水口位置，用六角扳手将螺钉拧紧。

确保O型圈套在塞扣上，塞上塞扣。



How to Install the Spout

Remove and retain the supply tee(6), the nuts(4, 5) and washer(3) from the shank(1) .

Fit the shank with washer(2) into the center hole of tub. Install the washer(3) and tighten the nut(4, 5) to secure the shank.

Thread supply tee(6) to the shank of the unit kit until hand-tight.

Remove the plug(12) and O-ring(11) in the back of spout. Loosen the screw(10) by hex wrench(9).

Install the escutcheon(7) on the shank, contach the deck or bath tub rim.

Install the spout(8) on the escutcheon, and make it against the escutcheon. position the spout, tighten the screw by hex wrench(9).

Place the o-ring on the plug, Press the plug into the hole.

如何安装阀体和把手

先从阀体组件(13)上取下装饰盖底座(14)和橡胶垫片(15)。


确保垫片(16)、钢垫(17)和安装环(18)在阀体上。

从浴缸下方将阀体组件装入浴缸安装孔(注：带红色标志的阀体组件装在左侧)。

将橡胶垫片(15)装到装饰盖底座底部凹槽中，将装饰盖底座装入阀体组件。

根据软管安装需要适当调整阀体出水口朝向。用螺丝刀拧紧螺钉(19)以固定阀体组件。

确保阀芯处于关闭状态。将把手组件(20)旋紧到装饰盖底座(14)。注意：带有“H”标记的把手组件装在左侧，带有“C”标记的把手组件装在右侧。



How to Install the Side Bodies and Handles

Remove the escutcheon base(14) and rubber washer(15) from the side body(13).


Make sure the washer(16), steel washer (17) and threaded ring(18) on the valve body.

Insert the side body into the mounting hole from the underside of the tub. **NOTE:** The side body with red mark should be installed on the left.

Put the rubber washer(15) into the bottom groove of the escutcheon base. Tighten the escutcheon base onto the valve body.

Adjust the outlet of side body to connect hose easily. Secure the side bodies by tightening screws(19) with screwdriver.

Ensure the valves are closed. Install the handle kits(20) onto the escutcheon base(14). **NOTE:** The handle kit with “H” mark should be installed on the left side. The handle kit with “C” mark should be installed on the right side.



如何连接软管


将垫片(22)放入软管(21)的两端，用软管将T型接头与两边的阀体组件(13)连接。

How to Connect the Hoses

Put the washers(22) into the end of the hoses(21). Connect the supply tee and side bodies(13) by hoses.

安装结果检查

INSTALLATION CHECKOUT



检查并确保所有的衔接处都已拧紧。确保手柄处于关闭位置。

打开排水系统和主要供水源，检查并修理有漏水的接口。

用工具(23)将起泡器(24)拆下，打开水龙头，让水流过出水口一分钟以清除杂质。

冲洗起泡器，关闭水龙头，重新装回起泡器。

Ensure that all connections are tight. Ensure that the handles are in the off position.

Open the drain. Turn on main water supply and check for leaks. Repair as required.

Remove aerator(23) by key(24). Turn on the faucet handles and run hot and cold water through spout for about one minute to remove any debris.

Remove any debris from aerator. Shut faucet off and reinstall aerator.

清洗说明

CLEANING INSTRUCTIONS

适用于所有加工处理过的表面：以中性肥皂水清洗镀层表面，再以干净的软布彻底擦干整个表面，许多清洁剂，比如氨水、去污粉及洁厕灵等，会对电镀表面造成伤害，切忌使用。

有磨损性的清洁用具或清洁剂也不可使用时于科勒牌的水龙头及其配件上。

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.