

Bellmore

With the luxurious touch of a fine linen textile, Bellmore offers a tactile sensory experience combined with the durability of porcelain and a palette that offers depth and warmth to any indoor or outdoor space.



12"x24" Metallic Gray and Metallic White

RECOMMENDED USE

- Suitable for indoor and outdoor wall and flooring applications, including commercial
- Suitable for installation on shower walls
- Suitable for high-temperature areas such as behind ranges and fireplace surrounds
- Outdoor use subject to climate and method of installation
- Material is not affected by freeze/thaw
- Suitable for submerged areas such as pools or fountains
- Testing data available upon request
- Please see Ann Sacks slip-resistance and wet flooring application statement to determine usage in a wet area



wall floor shower wall outdoor

INSTALLATION AND MAINTENANCE

- Install per industry standards for ceramic tile
- Always inspect material prior to installation — installed material cannot be accepted for return or credit
- Always lay out material prior to installation to properly blend and balance color



Bellmore contains 20-30% recycled content by color

ANN SACKS.

COLLECTION

Field	Field (non-rectified) 12"x24" Matte (11.750" x 23.625" x 0.354") 12"x24" Metallic (11.750" x 23.625" x 0.354") Field (rectified) 24"x48" Matte (23.625" x 47.625" x 0.354")
Material	Porcelain
Color	Matte 12"x24", 24"x48" Black, Gray, Ivory, Pearl, Sand, Smoke, Taupe, Tobacco, White Metallic 12"x24" Metallic Black, Metallic Gray, Metallic White
Lead Time	Non-stock. Typical lead times are 1-2 weeks <i>(Lead times are subject to change)</i>

*Please note: variations in color, shade, surface texture and size are natural characteristics of all our products and should be expected. Images shown are representative, but may not indicate all variations in these characteristics.

3/2023

www.annsacks.com | 1.800.278.8453

Bellmore

COLOR - MATTE



12"x24", 24"x48"
White



12"x24", 24"x48"
Ivory



12"x24", 24"x48"
Pearl



12"x24", 24"x48"
Sand




12"x24", 24"x48"
Taupe



12"x24", 24"x48"
Tobacco



12"x24", 24"x48"
Gray



12"x24", 24"x48"
Smoke



12"x24", 24"x48"
Black

*Please note: variations in color, shade, surface texture and size are natural characteristics of all our products and should be expected. Images shown are representative, but may not indicate all variations in these characteristics.

3/2023

Bellmore

COLOR - METALLIC



12"x24"
Metallic White



12"x24"
Metallic Gray



12"x24"
Metallic Black

*Please note: variations in color, shade, surface texture and size are natural characteristics of all our products and should be expected. Images shown are representative, but may not indicate all variations in these characteristics.

3/2023

ANN SACKS.

www.annsacks.com | 1.800.278.8453