

# Laurelhurst

This warm and natural stone-look porcelain is anything but basic. Offered in a range of natural colors, finishes and formats, this Italian porcelain was designed to be artfully combined. The versatile collection is ideal for both residential and commercial spaces, as well as interior and exterior projects.



24"x48" Natural in White

## COLLECTION

### RECOMMENDED USE

- Suitable for indoor and outdoor wall and flooring applications, including commercial
- Suitable for installation on shower walls
- Suitable for high temperature areas such as behind ranges and fireplace surrounds
- Outdoor use subject to climate and method of installation
- Material is not affected by freeze/thaw
- Suitable for submerged areas such as pools or fountains
- Formats and finishes have varying degrees of DCOF test results, though all pass the minimum requirement
- Testing data available upon request
- Please see Ann Sacks slip resistance and wet flooring application statement to determine usage in a wet area



### INSTALLATION AND MAINTENANCE

- Install per industry standards for ceramic tile
- Always inspect material prior to installation — installed material cannot be accepted for return or credit
- Always lay out material prior to installation to properly blend and balance color

<b>Field</b>	<b>Cracked</b> 24"x24" (23.622" x 23.622" x 0.394") Beige & Grey 24"x 48" (23.622" x 47.244" x 0.394") Beige & Grey
	<b>Flamed</b> 24"x48" (23.622" x 47.244" x 0.394") Grey & White
	<b>Grooved</b> 24"x48" (23.622" x 47.244" x 0.394") Beige, Grey & White
	<b>Hammered</b> 24"x48" (23.622" x 47.244" x 0.394") Beige, Grey & White
	<b>Happy</b> 24"x48" (23.622" x 47.244" x 0.394") White
	<b>Mixed</b> 3"x24" (2.953" x 23.622" x 0.394") Beige, Grey & White
	<b>Natural</b> 12"x24" (11.811" x 23.622" x 0.394") Beige, Grey & White 24"x48" (23.622" x 47.244" x 0.394") Beige, Grey & White
	<b>Patchy</b> 24"x48" (23.622" x 47.244" x 0.394") Grey
	<b>Peggy Glossy</b> 24"x48" (23.622" x 47.244" x 0.394") Beige
	<b>Mosaic</b>
<b>Trim</b>	3"x48" SBN (2.953" x 47.244" x 0.394") Beige, Grey & White
<b>Material</b>	Porcelain
<b>Color</b>	Beige, Grey, White

\*Please note: variations in color, shade, surface texture and size are natural characteristics of all our products and should be expected. Images shown are representative, but may not indicate all variations in these characteristics.

7/2024

# ANN SACKS.

[www.annsacks.com](http://www.annsacks.com) | 1.800.278.8453

# Laurelhurst

---

FIELD - BEIGE


---



Cracked  
24"x24"




Cracked  
24"x48"



Natural  
12"x24"  
24"x48"



Hammered  
24"x48"



Peggy Glossy  
24"x48"



Mixed  
3"x24"



Grooved  
24"x48"



SBN  
3"x48"

\*Please note: variations in color, shade, surface texture and size are natural characteristics of all our products and should be expected. Images shown are representative, but may not indicate all variations in these characteristics.

7/2024

# Laurelhurst

---

## FIELD - WHITE

---



Flamed  
24"x48"



Hammered  
24"x48"



Grooved  
24"x48"



Happy  
24"x48"



Natural  
12"x24"  
24"x48"



Mixed  
3"x24"

## MOSAIC/TRIM

---



1"x1.5" Mixed  
White



SBN  
3"x48"

\*Please note: variations in color, shade, surface texture and size are natural characteristics of all our products and should be expected. Images shown are representative, but may not indicate all variations in these characteristics.


7/2024

# Laurelhurst

---

## FIELD - GREY


---



Flamed  
24"x48"



Hammered  
24"x48"



Grooved  
24"x48"



Mixed  
3"x24"



Natural  
12"x24"  
24"x48"



Patchy  
24"x48"

## MOSAIC/TRIM - GREY

---



1"x2" Mixed



SBN  
3"x48"

\*Please note: variations in color, shade, surface texture and size are natural characteristics of all our products and should be expected. Images shown are representative, but may not indicate all variations in these characteristics.

7/2024