

# Solas

Solas offers a basic and effective program at a fantastic opening price point, allowing you to create a beautiful space within a limited budget.



3"x6" White Gloss

## RECOMMENDED USE

- Suitable for all indoor wall applications
- Suitable for installations on shower walls
- Suitable for high temperature areas such as behind and fireplaces surrounds
- Not suitable for flooring
- Not suitable for outdoor installation
- Not suitable for submerged areas such as pools or fountains



wall



shower wall

## INSTALLATION AND MAINTENANCE

- Please reference the TCNA handbook instructions for ceramic tile
- Always inspect material prior to installation, installed material cannot be accepted for return or credit
- Always lay out material prior to installation properly blend and balance color
- Clean only with a sponge or soft cloth using only neutral liquid soaps. Do not use cleaning products that contain hydrochloric acid, and/or potassium hydroxide.
- Recommended to seal tile and grout, especially in wet area installations, for ease of maintenance

## COLLECTION

<b>Field</b>	2"x8" Plain (1.890" x 7.752" x 0.335") 3"x6" Plain (2.933" x 5.965" x 0.335") 3"x9" Plain (2.933" x 8.957" x 0.335") 3"x12" Plain (2.933" x 11.969" x 0.335") 4"x8" Plain (3.858" x 7.787" x 0.335") 6"x24" Plain (5.866" x 23.622" x 0.335") 12"x24" Plain (11.811" x 23.622" x 0.335")
<b>Trims</b>	3"x6" SBN 3" Side (2.933" x 5.965" x 0.335") 3"x6" SBN 6" Side (2.933" x 5.965" x 0.335") 4"x8" SBN 4" Side (3.858" x 7.787" x 0.335") 4"x8" SBN 8" Side (3.858" x 7.787" x 0.335") 3"x6" Double SBN Right (2.933" x 5.965" x 0.335") 3"x6" Double SBN Left (2.933" x 5.965" x 0.335") 4"x8" Double SBN Right (3.858" x 7.787" x 0.335") 4"x8" Double SBN Left (3.858" x 7.787" x 0.335") 1"x6" Quarter Round (0.984" x 5.984" x 0.000") 1"x8" Quarter Round (0.984" x 7.795" x 0.000") 1"x12" Quarter Round (0.984" x 11.969" x 0.354") 1"x1.5" Cap Molding Stop (0.984" x 1.575" x 0.000") 1.5"x8" Cap Molding (1.575" x 7.835" x 0.906") 0.5" x 12" Feature Strip Plain (0.354" x 11.890" x 0.394") 0.5"x12" Pencil Bullnose (0.354" x 11.969" x 0.354") 1"x1" Pencil Bullnose Corner (0.984" x 0.984" x 0.000") 1" Beak (0.984" x 0.984" x 0.000")  <i>*Not all sizes available in all colors please consult our product matrix for availability</i>
<b>Material</b>	Ceramic
<b>Color</b>	Black Satin, Cream Gloss, White Gloss, White Matte
<b>Lead Time</b>	Non-stock. Typical Lead Times are 1-2 weeks <i>(Lead Times are subject to change)</i>

\*Please note: variations in color, shade, surface texture and size are natural characteristics of all our products and should be expected. Images shown are representative, but may not indicate all variations in these characteristics.

2/2020

# ANN SACKS.


[www.annsacks.com](http://www.annsacks.com) | 1.800.278.8453

# Solas


---

FIELD (Shown in White Matte)

---




2"x 8"




3"x 6"




3"x 9"




4"x 8"



3"x 12"



6"x 24"



12"x 24"

# Solas

---

FIELD (Shown in White Gloss)

---



3"x6" SBN 6" Side

Also available in:  
4"x8" SBN 8" Side



3"x6" SBN 3" Side

Also available in:  
4"x8" SBN 4" Side



3"x6" Double SBN Left

Also available in:  
3"x6" Double SBN Right  
4"x8" Double SBN Right  
4"x8" Double SBN Left



0.5"x12" Pencil Bullnose



1"x6" Quarter Round

Also available in:  
1"x8"  
1"x12"



1.5"x8" Cap Molding



1" Beak

*Not Shown: 1"x1.5" Cap Molding Stop  
0.5"x12" Feature Strip Plain  
1"x1" Pencil Bullnose Corner*

\*Please note: variations in color, shade, surface texture and size are natural characteristics of all our products and should be expected. Images shown are representative, but may not indicate all variations in these characteristics.

2/2020

**ANN SACKS.**

[www.annsacks.com](http://www.annsacks.com) | 1.800.278.8453

SOLAS COLOR AVAILABILITY MATRIX				
SIZE & DESIGN	COLOR			
	WHITE GLOSSY	WHITE MATTE	CREAM GLOSSY	BLACK SATIN
2" x8" Plain Field	√	√	√	√
3" x6" Plain Field	√	√	√	√
3"x9" Plain Field	√	√	√	√
3"x12" Plain Field	√	√	√	√
4"x8" Plain Field	√	√	√	√
6"x24" Plain Field	√	√		
12"x24" Plain Field	√	√		
3"x6" SBN 3" Side	√	√		
3"x6" SBN 6" Side	√	√		
4"x8" SBN 4" Side	√	√		
4"x8" SBN 8" Side	√	√		
3"x6" Double SBN Right	√	√		
3"x6" Double SBN Left	√	√		
4"x8" Double SBN Right	√	√		
4"x8" Double SBN Left	√	√		
1"x6" Quarter Round	√	√		
1"x8" Quarter Round	√	√		
1"x12" Quarter Round	√	√	√	√
1"x1.5" Cap Molding Stop	√	√	√	√
1.5"x8" Cap Molding	√	√	√	√
0.5"x12" Feature Strip Plain	√	√	√	√
0.5"x12" Pencil Bullnose	√	√	√	√
1"x1" Pencil Bullnose Corner	√	√	√	√
1" Beak	√	√	√	√

\*Please note: variations in color, shade, surface texture and size are natural characteristics of all our products and should be expected. Images shown are representative, but may not indicate all variations in these characteristics.

2/2020