

# Terrazzo Renata

Terrazzo Renata is our modern reinterpretation of a traditional Italian style. This stone is a mix of various sized flakes, grains and chips of precious marble, which creates a stunning graphic design for interiors.



16"x16" field in White

## RECOMMENDED USE

- Suitable for all indoor wall and flooring applications (except Fluted, which is suitable for wall only)
- Suitable for installation on shower walls
- Outdoor use subject to climate and method of installation
- Suitable for outdoors in non-freeze thaw climates
- Please see Ann Sacks slip-resistance and wet flooring application statement to determine usage in a wet area



## INSTALLATION AND MAINTENANCE

- Install per manufacturer's installation instructions
- It is recommended to seal natural stone with a penetrating sealer
- Periodic cleaning and resealing are recommended when using products formulated for natural stone — please reference the manufacturer's maintenance recommendations for approved cleaning products
- The use of acidic or highly alkaline detergents can damage the surface of the marble — please reference the manufacturer's maintenance recommendations for chemicals to avoid
- Always inspect material prior to installation — installed material cannot be accepted for return or credit
- Always lay out material prior to installation to properly blend and balance color



Terrazzo Renata Black, Grey and White contains 28% pre-consumer recycled content and is LEED v4 certified.

# ANN SACKS.

## COLLECTION

<b>Field</b>	<b>Field</b> 16"x16" (15.748" x 15.748" x 0.472") 24"x24" (23.622" x 23.622" x 0.472")  <b>Fluted Field</b> 12"x12" (11.811" x 11.811" x 1.181") <i>*Not available in Grey</i>  Other colors, sizes and finishes available via special order
<b>Mosaic</b>	2"x2" (Sheet: 11.811" x 11.811" x 0.472") <i>*Not available in Grey</i>
<b>Slab</b>	31"x84" (31.000" x 84.000" x 0.787")
<b>Material</b>	Various sized flakes, grains and chips of precious marble skillfully blended with resin
<b>Finish</b>	Honed
<b>Color</b>	Black (brushed black background with white stone) Cashmere (brushed cream background with white and grey stones) Grey (brushed grey background with white stone) Grigio Carnico (dark grey background with white and grey stone) White (brushed white background with white stone)
<b>Lead Time</b>	In-stock. Typical lead times are 1-2 weeks <i>(Lead times are subject to change)</i>

\*Please note: variations in color, shade, surface texture and size are natural characteristics of all our products and should be expected. Images shown are representative, but may not indicate all variations in these characteristics.

4/2023


[www.annsacks.com](http://www.annsacks.com) | 1.800.278.8453

# Terrazzo Renata


---

FIELD (Shown in Grigio Carnico)

---



16"x16"  
Grigio Carnico




24"x24"  
Grigio Carnico


## COLOR

---


*Not Shown: 31"x84" Slab*




White




Cashmere



Grey



Grigio Carnico



Black

\*Please note: variations in color, shade, surface texture and size are natural characteristics of all our products and should be expected. Images shown are representative, but may not indicate all variations in these characteristics.

4/2023

**ANN SACKS.**

[www.annsacks.com](http://www.annsacks.com) | 1.800.278.8453

# Terrazzo Renata


---

## FLUTED


---



12"x12" Fluted  
White



12"x12" Fluted  
Black



12"x12" Fluted  
Grigio Carnico


## MOSAIC

---


*Not Shown: Cashmere*



2"x2" Mosaic  
White



2"x2" Mosaic  
Black



2"x2" Mosaic  
Grigio Carnico

*Not Shown: Cashmere*

\*Please note: variations in color, shade, surface texture and size are natural characteristics of all our products and should be expected. Images shown are representative, but may not indicate all variations in these characteristics.

4/2023

# ANN SACKS.

[www.annsacks.com](http://www.annsacks.com) | 1.800.278.8453