KOHLER®

# Underscore® | K-1174-XHGH

72" x 42" drop-in Heated BubbleMassage™ air bath with whirlpool

## Features

- 122 airjets release thousands of heated bubbles that surround, support, and massage the body
- Variable-speed blower lets you adjust massage intensity to 18 levels
- Eight Proflex® hydromassage jets can be individually adjusted for water flow and direction
- Single-speed whirlpool offers performance and value with 8 fully adjustable jets
- Built-in heater
- Automatic and manual purge cycles remove residual water from air channels after use
- 60-minute automatic shutoff timer
- Slotted overflow allows for deep soaking
- Spacious design accommodates up to two bathers
- Integral lumbar support
- Keypad control
- Textured bottom surface

## Available Colors/Finishes

***Color tiles intended for reference only.***

| | | |
|---|---|---|
| | 0 | White |
| | 96 | Biscuit |
| | 95 | Ice Grey |
| | 7 | Black Black |



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-12-2026 11:15 - US-CA

THE BOLD LOOK OF KOHLER®

## Codes/Standards

ASME A112.19.7/CSA B45.10
CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662
UL 1795
CSA C22.2 No. 218.2
cUL Listed
UL Listed

## Technical Information

***All product dimensions are nominal.***

| | |
|---|---|
| Drain Location: | Center |
| Drain Hole Diameter: | 2-3/16" (56 mm) |
| Minimum Flat for Door: | 2-7/16" (61 mm) |
| Basin Area, Bottom: | 45-3/4" x 32" (1162 mm x 813 mm) |
| Basin Area, Top: | 65-7/16" x 35-3/8" (1662 mm x 898 mm) |
| Water Depth: | 19" (483 mm) |
| Water Capacity: | 139 gal (526.2 L) |
| Minimum Floor Load: | 64.1 lbs/ft$^2$ |
| Weight: | 203 lbs (92.1 kg) |
| Cutout: | Drop-in, 71-1/2" x 41-1/2" (1816 mm x 1054 mm) |

## Material

- Acrylic

## Recommended Products/Accessories

- K-1491 Bath/whirlpool pillow, removable
- K-1601 Bath/whirlpool footstop, removable
- K-706000-D3 56-5/8"-59-5/8" W x 62" H bypass bath door with 1/4"-thick Frosted glass
- K-706000-L 56-5/8"-59-5/8" W x 62" H bypass bath door with 1/4"-thick Crystal Clear glass
- K-706004-D3 56-5/8"-59-5/8" W x 62" H bypass bath door with 1/4"-thick Frosted glass
- K-706004-L 56-5/8"-59-5/8" W x 62" H bypass bath door with 1/4"-thick Crystal Clear glass
- K-706007-L 56-5/8"-59-5/8" W x 62" H sliding bath door with 3/8"-thick Crystal Clear glass

## Required Products/Accessories

- K-7271 Slotted overflow brass bath drain

or

- K-7272 Slotted overflow bath drain

## Technology

- Heated BubbleMassage™ technology warms and humidifies air before it enters the bath



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-12-2026 11:15 - US-CA

THE BOLD LOOK OF KOHLER.

## Required Electrical Service

Three dedicated circuits required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

| | |
|---|---|
| Blower: | 120 V, 15 A, 60 Hz |
| Heater, Pump: | 120 V, 15 A, 60 Hz |
| Heater: | 120 V, 15 A, 60 Hz |

## Electrical Component Ratings

| | |
|---|---|
| Power Cord Length: | 35" (889 mm) |
| Blower: | 120 V, 10 A |
| Heater: | 120 V, 5 A, 60 Hz |
| Pump: | 120 V, 7 A, 60 Hz |
| Heater: | 120 V, 12 A, 60 Hz |

## Warranty

***See website for detailed warranty information.***

KOHLER® Plastic Baths and Shower Bases Lifetime Limited Warranty
KOHLER® Hydrotherapy Components Five-Year Limited Warranty



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-12-2026 11:15 - US-CA

THE BOLD LOOK OF KOHLER.




## Installation

- Drop-in or undermount
- Center drain
- Requires Clearflo slotted overflow bath drain (sold separately)

## Installation Notes

***Install this product according to the installation instructions.***

Measure your actual product for rough-in details.
The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-12-2026 11:15 - US-CA

THE BOLD LOOK OF KOHLER