

## Features

- Chromatherapy lighting allows you to select a preferred color scheme to suit your mood
- Built-in heater
- Remote control
- Overflow channel for deep soak and unique infinity pool effect

## Material

- Acrylic

## Hydrotherapy

- 11 effervescence ports deliver gentle, caressing bubbles

## Installation

- Drop-in

## Required Products/Accessories

K-7193 Bath Drain

## Recommended Products/Accessories

K-1601 Bath/whirlpool footstop, removable

K-923 Wall- or -ceiling-mount bath filler

K-23726 Drain treatment

K-23732 Tub & shower cleaner



## Codes/Standards

ASME A112.19.7/CSA B45.10

CSA B45.5/IAPMO Z124

ASTM E162

ASTM E662

UL 1795

CSA C22.2 No. 218.2

IAPMO Certification

cUL Listed

UL Listed

## **KOHLER® Plastic Baths and Shower Bases Lifetime Limited Warranty** **KOHLER® Hydrotherapy Components Five-Year Limited Warranty**

See website for detailed warranty information.


## Available Colors/Finishes

*Color tiles intended for reference only.*



### Color Code Description

■ 0 White

No change in measurements if connected with drain illustrated. (K-7193)



Pump/Control Access  
 15" (381 mm) H x 40" (1016 mm) W Min



## Required Electrical Service

Two dedicated circuits required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Pump: 240 V, 20 A, 50/60 Hz  
 Heater: 240 V, 20 A, 50/60 Hz

## Technical Information

All product dimensions are nominal.

Drain location: Right  
 Basin area, bottom: 45" x 25-1/2" (1143 mm x 648 mm)  
 Basin area, top: 61-1/2" x 30-1/4" (1562 mm x 768 mm)  
 Weight: 275 lbs (124.7 kg)  
 Minimum floor load: 65 lbs/ft<sup>2</sup> (317.4 kg/m<sup>2</sup>)  
 Water depth: 23-1/2" (597 mm)  
 Water capacity: 142 gal (537.5 L)  
 Cutout: Drop-in, 73-1/2" x 39-1/2" (1867 mm x 1003 mm)  
 Electrical component rating: Pump: 240 V, 4 A, 50/60 Hz  
 Heater: 240 V, 15 A, 50/60 Hz, 4000 W

Pump speed: Variable

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada

7-9-2024 22:25 - US

## Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Consult local and national codes for minimum air gap requirements when installing a spout on the faucet deck.

Unit must be filled through the bathing well.