Composed® | K-181032-BC1

Touchless lavatory faucets and soap dispensers for Constellation™ lavatory system, 0.5 gpm

Features

- Touchless faucet, soap dispenser, and accessory combination designed for Constellation™ 60" wall-mount lavatory systems
- Faucets with Kinesis® technology and concealed sensors give a clean aesthetic and provide extraordinarily accurate and reliable actuation in varying installation environments
- 0.5 gpm (1.9 lpm) maximum flow rate
- On-demand usage with 30-second max. continual run cycle to prevent vandalism and save water
- Vandal-resistant aerators
- Soap dispensers possess adjustable volume and sensor range for precise actuations
- Soap dispenser requires low (1-20 cps or gr/m-s) viscosity foam soap with no suspended particles. Please see Installation Guide or Maintenance and Use Guide for specific soap recommendations
- Below-counter faucet valving and soap dispenser reservoirs reduce footprints and provide easier servicing
- Vandal-resistant sensor on soap dispenser delays dispensing for 30 seconds if blocked for ten seconds
- Above-counter low soap and low battery indicators
- Coordinating bag hooks hold purses, backpacks, and other bags
- Includes two assembled faucets and soap dispensers, two bag hooks, one multi-outlet power supply, four 10' (3.1 m) cable assemblies, two overflow assemblies, one 1-gallon bulk soap refill, mechanical mixing tee
- For installation requiring ASSE 1070 compliance, purchase thermostatic mixing valve (sold separately)

Sustainability

Available Colors/Finishes

Color tiles intended for reference only.

	CP	Polished Chrome
	BN	Vibrant Brushed Nickel
	BL	Matte Black
	2MB	Vibrant Brushed Moderne Brass

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-09-2026 07:01 - US-CA

THE BOLD LOOK OF KOHLER

Codes/Standards

ADA compliant when installed to the specific requirements of these regulations.

ADA

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 372
NSF/ANSI/CAN 61
UL 1310
ADA
ICC/ANSI A117.1

Technical Information

All product dimensions are nominal.

Spout

Spout Reach:	5-13/16" (148 mm)
Drain With Overflow:	[object Object]

Flow Rate

Faucet Flow Rate:	0.5 gpm (1.9 l/min)

Valves

Included Valve:	Thermostatic Mixer

Pressure/Fixture Supply Requirements

Minimum Flow Rate:	0.5 gpm (1.9 l/min)

Material

- Durable brass construction

Required Products/Accessories

- K-99799 Undercounter thermostatic mixing valve

Warranty

See website for detailed warranty information.

KOHLER® One-Year Limited Warranty

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-09-2026 07:01 - US-CA

THE BOLD LOOK OF KOHLER.



Installation

- Deck-mount

Installation Notes

Install this product according to the installation instructions.

For installations requiring ASSE 1070 compliance, purchase the 99799 NA thermostatic mixing valve (sold separately). One thermostatic mixing valve is required per faucet. ADA compliant when installed to the specific requirements of these regulations.

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-09-2026 07:01 - US-CA

THE BOLD LOOK OF KOHLER