



Underscore® Cube

Drop-In Whirlpool Bath
K-1969-H2

Features

- 8 hydromassage jets can be individually adjusted for water flow and direction.
- Variable-speed pump for adjusting massage intensity.
- Built-in heater.
- Lighted keypad.
- Remote control.
- Extra-deep square shape offers fully-immersed soaking experience with a compact footprint.
- Two integrated seats at different heights allow bathers to sit at their desired soaking depth.

Material

- Acrylic.

Hydrotherapy

- Whirlpool.

Installation

- Drop-in.

Required Products/Accessories

K-9698 Flexjet® Whirlpool Trim Kit

Recommended Products/Accessories

K-8134 Cable Bath Drain Trim Kit
K-8150 Cube Cable Drain
K-24916 Wireless Music Kit
K-578 Cube Undermount Installation Kit
K-1491 Bath/Whirlpool Pillow
K-1601 Bath/Whirlpool Footstop
K-1177 Vinyl Tiling-in Bead
K-23726 Drain treatment
K-23732 Tub & shower cleaner



Codes/Standards

ASME A112.19.7/CSA B45.10
CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662
UL 1795
CSA C22.2 No. 218.2

KOHLER® Plastic Baths and Receptors
Lifetime Limited Warranty
KOHLER® Hydrotherapy Components
Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
	96	Biscuit




Underscore® Cube

Drop-In Whirlpool Bath

K-1969-H2

No change in measurements if connected with drain illustrated. (K-8150)



Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Heater, Pump: 240 V, 20 A, 50/60 Hz

Technical Information

All product dimensions are nominal.

Installation:	Drop-in
Drain location:	Center
Basin area, bottom:	39-3/8" x 39-3/8" (1000 mm x 1000 mm)
Basin area, top:	44-5/8" x 44-5/8" (1134 mm x 1134 mm)
Weight:	150 lbs (68 kg)
Minimum floor load:	100 lbs/ft ² (488.2 kg/m ²)
Water depth:	27-1/16" (687 mm)
Water capacity:	171 gal (647.3 L)
Electrical component rating:	Heater: 240 V, 50/60 Hz, 1500 W Pump: 240 V, 15 A, 50/60 Hz, 1500 W

Notes

Measure your actual product for rough-in details. Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Kit is required for under-mount installations (sold separately).

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com.

4-14-2020 06:28 - US/CA

THE BOLD LOOK
OF **KOHLER**