



Underscore® | K-1969-JH

48" x 48" heated whirlpool bath with center drain

Features

- Eight Proflex® hydromassage jets can be individually adjusted for water flow and direction
- Variable-speed pump for adjusting hydromassage intensity
- Built-in heater
- Extra-deep square shape offers fully-immersed soaking experience with a compact footprint
- Spacious design accommodates up to two bathers
- Two integral corner seats
- Integral lumbar support
- Textured bottom surface



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-30-2026 02:03 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

ASME A112.19.7/CSA B45.10
CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662
UL 1795
CSA C22.2 No. 218.2
cUL Listed
UL Listed

Technical Information

All product dimensions are nominal.

Drain Location:	Center
Basin Area, Bottom:	39-3/8" x 39-3/8" (1000 mm x 1000 mm)
Basin Area, Top:	43-11/16" x 43-11/16" (1109 mm x 1109 mm)
Water Depth:	29" (736 mm)
Water Capacity:	171 gal (647.3 L)
Minimum Floor Load:	100 lbs/ft ²
Weight:	160 lbs (72.6 kg)
Cutout:	Drop-in, 47" x 47" (1194 mm x 1194 mm)

Material

- Acrylic

Recommended Products/Accessories

K-1491 Bath/whirlpool pillow, removable
K-1601 Bath/whirlpool footstop, removable
K-1177 Tiling-in bead, 144" length

Required Products/Accessories

- K-9698 Whirlpool trim kit with eight jets

Required Electrical Service

Two dedicated circuits required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Pump:	120 V, 15 A, 60 Hz
Heater:	120 V, 15 A, 60 Hz

Electrical Component Ratings


Pump:	120 V, 7 A, 60 Hz
Heater:	120 V, 12 A, 60 Hz

Warranty


See website for detailed warranty information.

KOHLER® Plastic Baths and Shower Bases Lifetime Limited Warranty|KOHLER® Hydrotherapy Components Five-Year Limited Warranty






No change in measurements if connected with drain illustrated. (K-8150)



Drop-in Rim Detail



Installation

- Drop-in or undermount
- Center drain

Installation Notes

Install this product according to the installation instructions.

Measure your actual product for rough-in details.
The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

