Pinoir® | K-2035-1

22" oval wall-mount bathroom sink

Features

- Single faucet hole
- Oval basin
- Overflow drain
- Combination consists of basin and shroud

Available Colors/Finishes

Color tiles intended for reference only.

0 White

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-12-2026 10:45 - US-CA

Codes/Standards

ADA, OBC compliant when installed to the specific requirements of these regulations.

ADA OBC

ASME A112.19.2/CSA B45.1
ADA
ICC/ANSI A117.1
OBC

Technical Information

Number of Deck Holes:	1
Faucet Hole(s) Size:	1-3/8" (35 mm)
With Overflow:	Yes
Drain Hole Diameter:	1-3/4" (44 mm)
Basin Configuration:	Single Bowl
Basin Length:	18" (457 mm)
Basin Width:	12" (305 mm)
Basin Depth:	6" (153 mm)

Material

- Vitreous china

Included Combo Skus

- K-2028-1 22" oval wall-mount bathroom sink
- K-2057 Bathroom sink shroud

Recommended Products/Accessories

- [object Object]23726 Drain treatment
- K-7605-P Pair 3/8" NPT angle supplies with stop, cross handle and annealed vertical tube
- K-8998 Adjustable P-trap with tubing outlet, 1-1/4" x 1-1/4"
- K-23725 Cast iron cleaner

Warranty

See website for detailed warranty information.

KOHLER® Vitreous China Bathroom Sink Lifetime Limited Warranty

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-12-2026 10:45 - US-CA

THE BOLD LOOK OF KOHLER.



Recommended ADA Installation

Installation

- Wall-mount

Installation Notes

Install this product according to the installation instructions.

Product dimensions are nominal and may vary per ASME A112.19.2 tolerances.
ADA, OBC compliant when installed to the specific requirements of these regulations.

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-12-2026 10:45 - US-CA

THE BOLD LOOK OF KOHLER.