

Graze® Semi-professional kitchen sink faucet with threefunction sprayhead

K-22061

Features

- Semi-professional kitchen faucet with finish-matched easyclean hose cover
- Switch-Grip[™] sprayhead rotates in 90-degree increments. Face buttons in the direction you prefer
- Three-function pull-down sprayhead with touch-control allows you to switch between stream, Sweep® spray and BerrySoft® spray
- Sweep® spray features specially angled nozzles that form a wide, powerful blade of water to sweep your dishes and sink clean
- DockNetik® magnetic docking system securely locks sprayhead into place when not in use
- 21" high-arch 360° rotating swing spout offers vertical clearance for tall cookware and pitchers
- 10" (254 mm) swing spout reach
- 1.5 gpm (5.7 lpm) maximum flow rate at 60 psi (4.14 bar)
- Single lever handle makes adjusting water temperature easy.
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage
- MasterClean[™] sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Deck-mount
- Single-hole installation (three-hole escutcheon sold separately)
- Flexible supply lines simplify installation

Adapters, Rough-in and Extension Kits

1327990

Range: 2-1/2" (64 mm) -4-5/8" (117 mm)

Optional Products/Accessories

K-22071 Three-hole kitchen faucet escutcheon





Codes/Standards

ASME A112.18.1/CSA B125.1 NSF/ANSI/CAN 61 NSF/ANSI/CAN 372 All applicable US Federal and State material regulations DOE - Energy Policy Act 1992 California Energy Commission (CEC) ADA ICC/ANSI A117.1 CSA B651 IAPMO Certification

KOHLER[®] Faucet Lifetime Limited Warrantv


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

CP	Polished Chrome
SN	Vibrant® Polished Nickel
AF	Vibrant® French Gold
VS	Vibrant® Stainless
BV	Vibrant® Brushed Bronze
BL	Matte Black
2MB	Vibrant® Brushed Moderne
тт	Brass Vibrant Titanium




Kohler Co. reserves the right to make revisions without notice to product specifications. For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada 10-21-2024 00:49 - US/CA



Graze®

KOHLER. Faucets

Semi-professional kitchen sink faucet with threefunction sprayhead K-22061



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 1.5 gal/min (5.7 l/min)

Drain included:

Spout:

Spout reach:

Handle clearance: 5-1/4" (133 mm)

10" (254 mm)

No

Handshower:

Rated maximum flow:

0 gal/min (0 l/min)

Notes

Install this product according to the installation instructions.

ADA complaint for faucet handles only. ADA compliant for faucet handles only ADA, CSA B651 compliant when installed to the specific requirements of these regulations.

