

#### Crue® Semi-professional kitchen sink faucet with threefunction sprayhead K-22973

Features

- Professional-style faucet with an easy-to-clean coated hose and removable coil
- Three-function pull-down sprayhead with touch-control allows you to switch between stream, Sweep<sup>®</sup> spray and Boost technology
- Sweep® spray features specially angled nozzles that form a wide, powerful blade of water to sweep your dishes and sink clean
- Boost technology increases the flow rate by 30% with the press of a button. Use Boost with stream for faster filling or with Sweep<sup>®</sup> spray for more powerful cleaning
- DockNetik® magnetic docking system securely locks sprayhead into place when not in use
- ProMotion<sup>®</sup> technology's light, quiet braided hose and swiveling ball joint make the pull-down sprayhead easier and more comfortable to use
- MasterClean<sup>™</sup> sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- High-arch spout offers vertical clearance for tall cookware and pitchers
- Single lever handle makes adjusting water temperature easy.
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage
- KOHLER<sup>®</sup> ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- 1.5 gpm (5.7 lpm) maximum flow rate at 60 psi (4.14 bar)

#### Material

- Premium metal construction for durability and reliability
- KOHLER<sup>®</sup> finishes resist corrosion and tarnishing

#### Installation

- Single-hole or three-hole installation (escutcheon plate included)
- Flexible supply lines simplify installation

#### **Recommended Products/Accessories**

K-77685 Single-cartridge water filtration system K-77686 Double-cartridge water filtration system K-77687 single replacement filter cartridge K-77688 Replacement Filter Cartridges, Two-Pack

#### **Optional Products/Accessories**

K-22071 Three-hole kitchen faucet escutcheon





#### Codes/Standards

ASME A112.18.1/CSA B125.1 NSF/ANSI/CAN 61 NSF/ANSI/CAN 372 All applicable US Federal and State material regulations DOE - Energy Policy Act 1992 California Energy Commission (CEC) ADA ICC/ANSI A117.1 CSA B651 IAPMO Certification

# KOHLER<sup>®</sup> Faucet Lifetime Limited Warranty

See website for detailed warranty information.

## **Available Colors/Finishes**

Color tiles intended for reference only.


#### Color Code Description



# Crue®

KOHLER, Faucets

Semi-professional kitchen sink faucet with threefunction sprayhead K-22973



#### **Technical Information**

All product dimensions are nominal.

#### Faucet:

Flow rate: 1.5 gal/min (5.7 l/min)

No

Drain included:

Spout:

Spout reach:

9" (229 mm)

#### Handshower:

Rated maximum 0 gal/min (0 l/min) flow:

## **Pressure/fixture Supply Requirements**

Fixture pressure 125 psi (861.8 kPa) max (static): Fixture pressure min 20 psi (137.9 kPa)

Fixture pressure min 20 psi (137.9 kPa) (static):

#### Notes

Install this product according to the installation instructions.

ADA complaint for faucet handles only. ADA compliant for faucet handles only ADA, CSA B651 compliant when installed to the specific requirements of these regulations.

