



# Crue® | K-22974-WB

Touchless pull-down kitchen sink faucet with KOHLER® Konnect™ and three-function sprayhead

## Features

- Touchless on/off with a wave of your hand or an object such as a pan
- Response® technology uses a state-of-the-art motion sensor for reliable touchless activation
- AC-powered operation—no batteries to replace
- Voice control allows hands-free activation to turn the faucet on or off, pour specific amounts and fill preset measurements.\*
- KOHLER Konnect® pairs with Amazon Alexa and Google Home\*\*
- Innovative sensor monitors water usage and displays that information on the KOHLER Konnect® app
- Notification can be sent to your mobile device when unusual flow of water is detected.\*\*\*
- 2.4 GHz password-protected Wi-Fi connection is required
- Three-function pull-down sprayhead with touch control allows you to switch between aerated stream, ring spray and Boost technology
- DockNetik® secure docking system locks sprayhead into place when not in use
- ProMotion® technology's light, quiet braided hose and swiveling ball joint make the pull-down sprayhead easier and more comfortable to use
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- 1.5 gpm (5.7 lpm) maximum flow rate at 60 psi (4.14 bar)
- \*When dispensing measured amounts, minimum of 8 oz. is required; accuracy may vary depending on water pressure and flow rate



## Sustainability



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications. For the most current specification sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada.  
4-15-2026 5:50 - US-CA

THE BOLD LOOK  
OF **KOHLER**

## Codes/Standards

ADA, CSA B651 compliant when installed to the specific requirements of these regulations.

ADA    CSA B651

ASME A112.18.1/CSA B125.1  
 NSF/ANSI/CAN 372  
 NSF/ANSI/CAN 61  
 DOE - Energy Policy Act 1992  
 California Energy Commission (CEC)  
 ADA  
 ICC/ANSI A117.1  
 CSA B651

## Technical Information

All product dimensions are nominal.

### Handle

Handle Style/ Type:                      Lever

### Spout

Spout Reach:                                8-9/16" (217 mm)

### Flow Rate

Faucet Flow Rate:                        1.5 gpm (5.7 l/min)

## Valves

Included Valves:                          Ceramic disc, Thermostatic, Volume Control

## Recommended Products/Accessories

K-22071 Three-hole kitchen faucet escutcheon

## Technology

- \*\*\*Notification through the KOHLER Konnect® app can advise you when water flow is detected beyond the flow sensor greater than 0.5 gpm for 3 seconds. (Not to be relied upon for water leak detection.)

## Connectivity



Amazon, Alexa and all related logos are trademarks of Amazon, Inc. or its affiliates.

Google, Google Home and Google Play are trademarks of Google LLC.

## Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

120 V, 0.15 A, 50/60 Hz

## Electrical Component Ratings


Power Cord Length:                      72" (1829 mm)

## Warranty

See website for detailed warranty information.

KOHLER® Electronic Faucets, Valves, and Controls Five-Year Limited Warranty|KOHLER® Faucet Lifetime Limited Warranty





## Installation

- Requires nonswitched undercounter outlet
- Single-hole or three-hole installation (escutcheon plate included)
- Google, Google Home and Google Play are trademarks of Google LLC

## Installation Notes

*Install this product according to the installation instructions.*

ADA compliant for faucet handles only  
 ADA, CSA B651 compliant when installed to the specific requirements of these regulations.

