

Semi-professional kitchen sink faucet with threefunction sprayhead

K-24982

Features

- Professional-style faucet with an easy-to-clean coated hose and removable coil
- Unique three-function sprayhead with Sweep[®] spray, Boost technology and aerated stream
- Handle rotates 90° forward to prevent contact with backsplash
- Sweep[®] spray creates a wide, forceful blade of water for superior cleaning
- Boost technology increases the flow rate by 30% with the press of a button
- DockNetik® magnetic docking system securely locks sprayhead into place when not in use
- MasterClean[™] sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Single lever handle is simple to use and makes adjusting water temperature easy
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- 1.5 gpm (5.7 lpm) maximum flow rate at 60 psi (4.14 bar)

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Single hole
- Flexible supply lines simplify installation

Adapters, Rough-in and Extension Kits

1327990 Range: 2-1/2" (64 mm) -4-5/8" (117 mm)

Recommended Products/Accessories

K-23723 Faucet cleaner





Codes/Standards

ASME A112.18.1/CSA B125.1 NSF/ANSI/CAN 61 NSF/ANSI/CAN 372 All applicable US Federal and State material regulations DOE - Energy Policy Act 1992 California Energy Commission (CEC) ADA ICC/ANSI A117.1 CSA B651 IAPMO Certification

KOHLER[®] Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

CP	Polished Chrome
SN	Vibrant® Polished Nickel
AF	Vibrant® French Gold
VS	Vibrant® Stainless
BV	Vibrant® Brushed Bronze
BL	Matte Black
2MB	Vibrant® Brushed Moderne
тт	Brass Vibrant Titanium

1-800-4KOHLER (1-800-456-4537)


Kohler Co. reserves the right to make revisions without notice to product specifications. For the most current Specification Sheet, go to <u>www.kohler.com</u> USA or <u>www.kohler.ca</u> Canada 10-20-2024 23:04 - US/CA



Purist®

KOHLER, Faucets

Semi-professional kitchen sink faucet with threefunction sprayhead K-24982



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 1.5 gal/min (5.7 l/min)

No

Drain included:

Handshower:

Rated maximum flow:

0 gal/min (0 l/min)

Notes

Install this product according to the installation instructions.

ADA complaint for faucet handles only. ADA compliant for faucet handles only ADA, CSA B651 compliant when installed to the specific requirements of these regulations.

