

KOHLER® Faucets

Single-function showerhead and wireless speaker with
Amazon Alexa, 2.5 gpm
Moxie®
K-28238-NKA

Features

- Full coverage spray produces an encompassing spray ideal for everyday use
- Best-in-class audio with sound by Harman Kardon®
- Easily toggle between two sound-performance settings, "Shower" and "Normal," depending upon where speaker is being used
- IPX7-rated waterproof speaker
- Magnetic showerhead holds speaker securely in place, yet removes easily for charging
- Built-in microphones tune out background noise for clearer voice command detection
- Featuring BLUETOOTH® wireless technology, allowing you to pair any compatible device to stream your favorite music, podcast, or other audio content
- Amazon Alexa-enabled so you can ask to play music, hear the news, check weather, control smart home devices, and more
- Wireless speaker can be used outside the shower space, independent of the showerhead, to stream music in any room
- Speaker provides up to 5-1/2" hours of play time
- Charging dock quickly and easily charges speaker
- Download the KOHLER Konnect® app for additional functionality

Material

- Durable material construction
- KOHLER finishes resist corrosion and tarnishing

Installation

- Wall-mount
- Shower arm and flange sold separately

Recommended Products/Accessories

K-7395 Shower Arm and Flange





Codes/Standards

ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992
NOM Standards
NOM 008-CONAGUA

KOHLER® One-Year Limited Warranty KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

The BLUETOOTH® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Kohler Co. is under license. Other trademarks and trade names are those of their respective owners.



Technical Information

All product dimensions are nominal.

Power source: Battery - DC, not included

Electrical component Speaker: 10 W rating:

Amplifier channels: 1 at 10 W per channel

Spout:

Charge time: 3 hours

Usage time: 5 hours

Bluetooth® range: 32.8 ft (10 m)

Bluetooth® version: 5.0

Max. Ambient temp: 140°F (60°C)

Frequency response: 65 Hz - 20 kHz +/-

Signal to noise ratio: >70 dB

Shower/Rainhead rated max flow: 2.5 gal/min (9.5 l/min)

Notes

Install this product according to the installation instructions.

Follow local building electrical codes.

A Bluetooth® wireless device is required to stream music

For use with automatic compensating valves rated at 2.00 gal/min (7.6 L./min) or less.