

KOHLER[®] Faucets

Single-function showerhead with wireless speaker, 2.5 gpm
Moxie[®]
K-28238-NKE

Features

- Full coverage spray produces an encompassing spray ideal for everyday use
- Best-in-class audio with sound by Harman Kardon[®]
- Easily toggle between two sound-performance settings, "Shower" and "Normal," depending upon where speaker is being used
- IPX7-rated waterproof speaker
- Magnetic showerhead holds speaker securely in place, yet removes easily for charging
- Featuring BLUETOOTH[®] wireless technology, allowing you to pair any compatible device to stream your favorite music, podcast, or other audio content
- Wireless speaker can be used outside the shower space, independent of the showerhead, to stream music in any room
- Speaker provides up to nine hours of play time
- Charging dock quickly and easily charges speaker
- Download the KOHLER Konnect[®] app for additional functionality

Material

- Durable material construction
- KOHLER[®] finishes resist corrosion and tarnishing

Installation

- Wall-mount
- Shower arm and flange sold separately

Recommended Products/Accessories

K-7395 Shower Arm and Flange



Codes/Standards

ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992
IAPMO Certification

KOHLER[®] One-Year Limited Warranty KOHLER[®] Faucet Lifetime Limited Warranty

See website for detailed warranty information.

The BLUETOOTH[®] word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Kohler Co. is under license. Other trademarks and trade names are those of their respective owners.

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

10-22-2024 21:44 - US/CA




THE BOLD LOOK
OF **KOHLER**[®]

KOHLER Faucets Single-function showerhead with wireless speaker, 2.5

Moxie®

gpm

K-28238-NKE



Technical Information

All product dimensions are nominal.

Power source: Battery - DC, included

Electrical component rating: Speaker: 10 W

Amplifier channels: 1 at 10 W per channel

Handshower:

Rated maximum flow: 0 gal/min (0 l/min)

Charge voltage: USB 5 V

Charge time: 3 hours

Usage time: 9 hours

Bluetooth® range: 32.8 ft (10 m)

Bluetooth® version: 5.0

Max. Ambient temp: 140°F (60°C)

Frequency response: 65 Hz - 20 kHz +/-

Signal to noise ratio: >70 dB

Showerhead/Body Spray:

Rated maximum flow: 2.5 gal/min (0.5 l/min)

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

10-22-2024 21:44 - US/CA

Notes

Install this product according to the installation instructions.

Follow local building electrical codes.

A Bluetooth® wireless device is required to stream music.

For use with automatic compensating valves rated at 2.00 gal/min (7.6 L./min) or less.

THE BOLD LOOK
OF **KOHLER®**