



Tempered™ | K-28874

35-3/4" undermount single-bowl farmhouse workstation kitchen sink with tall apron

Features

- Fits minimum 36" (914 mm) apron sink base cabinet
- Single large bowl
- 9" (229 mm) depth provides generous workspace
- Self-Trimming® apron overlaps cabinet face for easy installation and beautiful results
- Bowl slopes toward drain to minimize water pooling
- Offset drain increases workspace in the sink and storage space underneath
- No faucet holes; requires wall- or counter-mount faucet
- Integrated knife holder provides a convenient spot to dry or place your kitchen knives during food preparation
- Custom-designed grated rack rests on sink bevel and functions as a drying rack or convenient shelf for rinsing and defrosting
- Handcrafted walnut cutting board locks securely into rack for effortless cutting and chopping of ingredients
- Box includes: Sink, walnut cutting board, knife holder, drying rack, cutout template, installation hardware
- Sink strainer sold separately



Sustainability



Available Colors/Finishes

Color tiles intended for reference only.

0	White
FF	Sea Salt
96	Biscuit
NY	Dune
95	Ice Grey
7	Black Black



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-30-2026 04:28 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

ASME A112.19.1/CSA B45.2

Technical Information

All product dimensions are nominal.

Drain Hole Diameter:	3-7/8" (98 mm)
Minimum Base Cabinet Width:	36" (914 mm)
Basin Configuration:	Single Bowl
Basin Length:	30-1/4" (769 mm)
Basin Width:	15-13/16" (402 mm)
Basin Depth:	9" (229 mm)

Material

- KOHLER® enameled cast iron
- Acid-resistant enamel finish

Recommended Products/Accessories

K-6239 Rinsing colander with cutting board
 K-6237 Left-hand sink rack
 K-23726 Drain treatment
 K-6255 Right-hand sink rack
 K-23725 Cast iron cleaner
 K-8801 Sink drain and strainer with tailpiece
 K-8799 Sink drain and strainer basket, less tailpiece
 K-11352 Disposal flange with stopper
 K-9000 Adjustable P-trap with tubing outlet, 1-1/2" x 1-1/2"


Warranty

See website for detailed warranty information.

KOHLER® Enameled Cast Iron Kitchen and Bathroom Sink
 Lifetime Limited Warranty



1-800-4KOHLER (1-800-456-4537)
 Kohler Co. reserves the right to make revisions without notice to product specifications.
 For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
 7-30-2026 04:28 - US-CA



Installation

- For 36" (914 mm) apron-front cabinetry
- Undermount

Installation Notes

Install this product according to the installation instructions.



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

7-30-2026 04:28 - US-CA