Iron/Impressions® | K-3051-8

37" Enameled cast iron vanity top with integrated oval sink

Features

- 8" (203 mm) widespread faucet holes
- Elongated oval basin

Sustainability

ENDURES FOR GENERATIONS

Available Colors/Finishes

Color tiles intended for reference only.

	0	White
	FF	Sea Salt
	96	Biscuit
	NY	Dune
	95	Ice Grey
	FT	Basalt
	7	Black Black
	GRL	Lavender Grey
	DGB	Indigo Blue
	PLM	Black Plum

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-18-2026 00:01 - US-CA

THE BOLD LOOK OF KOHLER

Codes/Standards

ASME A112.19.1/CSA B45.2

Technical Information

Number of Deck Holes:	3
Faucet Hole(s) Size:	1-3/8" (35 mm)
Center(s):	8" (203 mm)
Drain Hole Diameter:	1-3/4" (44 mm)
Basin Configuration:	Single Bowl
Basin Length:	32" (813 mm)
Basin Width:	13-7/8" (352 mm)
Basin Depth:	4-15/16" (125 mm)

Material

- KOHLER® enameled cast iron

Recommended Products/Accessories

- [object Object]23726 Drain treatment
- K-9018 Adjustable P-trap with long tubing outlet, 1-1/4" x 1-1/4"
- K-23725 Cast iron cleaner
- K-99543-R 36" wall-hung bathroom vanity cabinet

Warranty

See website for detailed warranty information.

KOHLER® Enameled Cast Iron Kitchen and Bathroom Sink Lifetime Limited Warranty

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-18-2026 00:01 - US-CA

THE BOLD LOOK OF KOHLER.



Installation

- Vanity top

Installation Notes

Install this product according to the installation instructions.

NOTE: When selecting a faucet for this bathroom sink, ensure the faucet has a spout reach of 4-1/2" (114 mm) to 5" (127 mm) and has a spout height of 3" (76 mm) to 6" (152 mm).
Product does not have an overflow.

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-18-2026 00:01 - US-CA

THE BOLD LOOK OF KOHLER.