



## Landshapes™ by Daniel Arsham

14-3/4" pendant  
**K-32695-PELED**

### Features

- Designed in collaboration with Daniel Arsham
- A delicate glass sheet drapes over a sphere of light creating a warm luminosity
- Integrated LED
- Suitable for damp locations, per UL 1598
- Downrods offer additional height options
- Includes installation hardware
- Coordinates with other products in the Landshapes™ by Daniel Arsham collection

### Material

- Premium metal and glass construction
- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

### Installation

- Ceiling-mount

### Recommended Products/Accessories

K-32131 69-1/2" x 34-1/2" freestanding bath (Qty 2)  
K-32263 Triangular cabinet knob (Qty 2)  
K-32300 21-1/2" oval vessel bathroom sink, no overflow (Qty 2)  
K-32316 61" Dekton® vanity top (Qty 2)  
K-32576 (Qty 2)  
K-32624 3" x 12" feature tile produced by the KOHLER WasteLAB (Qty 2)  
K-32639 6" x 6" feature tile produced by the KOHLER WasteLAB (Qty 2)  
K-5401-DA One-piece elongated smart toilet, dual-flush (Qty 2)  
K-T77981-CLG Wall-mount bathroom sink faucet handle trim (Qty 2)  
K-32693-SCLED One-light LED sconce  
K-32694-SCLED One-light LED sconce



### Codes/Standards

UL 1598  
CSA C22.2 No. 250.0

### KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	BNL	Brushed Nickel
	CPL	Polished Chrome
	BLL	Matte Black
	2GL	Brushed Moderne Brass

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada



4-21-2025 22:50 - US/CA

THE BOLD LOOK  
OF **KOHLER®**



## Landshapes™ by Daniel Arsham

14-3/4" pendant  
**K-32695-PELED**



### Required Electrical Service

One circuit required.

Lights: 120 V, 1 A, 60 Hz

### Technical Information

All product dimensions are nominal.

Material: Steel, Glass

Number of Lights: 1

Lighting Type: Integrated LED

Number of Shades: 1

Shade Type: Painted Glass

Hanging Type: Downrod

CRI  $\geq 90$

Life Span 50000 Hours

Downrod Detail: 2 x 18" (457 mm), 1 x 12" (305 mm), 1 x 6" (152 mm), 1 x 3" (76 mm)

Height: 18-1/2" (470 mm) - 71-1/2" (1816 mm)

Electrical component rating: LED: 17 W, 2045 Lumens

### Notes

Install this product according to the installation instructions.

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada

4-21-2025 22:50 - US/CA

THE BOLD LOOK  
OF **KOHLER**®