



Persuade® | K-3654

Two-piece compact elongated toilet with skirted trapway, dual-flush

Features

- Two-piece design
- Compact elongated bowl offers added comfort while occupying the same space as a round-front bowl
- Top-mounted two-button flush offers a choice of 1.0 or 1.6 gallons per flush (gpf)
- Skirted trapway simplifies cleaning
- Combination consists of toilet bowl and tank
- Dual-flush technology allows you to choose between a full or partial flush
- Eligible for consumer rebates in some municipalities
- This product can help a building earn Water Efficiency points in LEED® Green Building Rating System



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-08-2026 18:48 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

Accessibility standards may require controls to be located on the open side of the toilet.



ASME A112.19.2/CSA B45.1
ASME A112.19.14
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)

Warranty

See website for detailed warranty information.

KOHLER® One-Year Limited Warranty

Technical Information

Rough-in:	Standard 12" (305mm)
Flush Type:	Dual-Flush Technology
Flush Rate:	1.0 or 1.6 gpf (3.8 or 6 lpf)
Bowl Shape:	Elongated
Seat-Mounting Holes:	5-1/2" (140 mm)
Waste Outlet:	Floor
Trapway Size:	2" (51 mm)
Trapway Type:	Skirted
Water Surface Size:	4-1/2" x 5-3/4" (114 mm x 146 mm)
Rim to Water Surface:	8-1/2" (216 mm)


Included Combo Skus

- K-4322 Compact elongated toilet bowl with skirted trapway
- K-4419 Toilet tank, dual-flush

Recommended Products/Accessories

- [object Object]23726 Drain treatment
- K-5588 Deodorizing elongated toilet seat





Installation

- Standard 12" (305 mm) rough-in
- Two-bolt installation
- Seat and supply line sold separately

Installation Notes

Install this product according to the installation instructions.

IMPORTANT! The rough-in must be 12" (305 mm) or more from the base of the wall or baseboard. The base of the toilet fits tightly against the wall or baseboard. The toilet will not fit correctly if there is less than 12" (305 mm) of clear space between the base of the wall or baseboard and the centerline of the outlet. Install or relocate the supply and outlet as necessary to conform to rough-in dimensions.

NOTE: If a baseboard causes the rough-in to be less than 12" (305 mm), it must be cut or removed to allow space for the toilet.

If this toilet is installed in new construction, install a new supply stop following the dimensions in the diagram. In installations with the supply stop installed, the existing supply stop may need to be relocated if it is less than 8-1/2" (216 mm) from the centerline of the toilet. Dry fit the toilet to confirm if the supply stop needs to be relocated.



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications. For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada. 10-08-2026 18:48 - US-CA

THE BOLD LOOK
OF **KOHLER.**