Triton® Bowe® | K-400T20-4AKA

1.0 gpm centerset bathroom sink faucet with aerated flow and lever handles, drain not included

Features

- Quarter-turn washerless ceramic disc valves
- Vandal-resistant aerated flow
- Lever handles
- Less drain
- 1.0 gpm (3.8 lpm) maximum flow rate at 60 psi (4.14 bar)

Sustainability

WATER-SAVING DESIGN

Available Colors/Finishes

Color tiles intended for reference only.

CP Polished Chrome

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-08-2026 22:12 - US-CA

THE BOLD LOOK OF KOHLER

Codes/Standards

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

ADA CSA B651 OBC

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 372
NSF/ANSI/CAN 61
DOE - Energy Policy Act 1992
EPA WaterSense®
ADA
ICC/ANSI A117.1
CSA B651
OBC

Technical Information

All product dimensions are nominal.

Handle

Handle Style/Type:	Lever

Spout

Spout Reach:	3-15/16" (99 mm)

Flow Rate

Faucet Flow Rate:	1 gpm (3.8 l/min)

Valves

Included Valves:	Ceramic disc, Thermostatic Mixer

Material

- Solid-brass construction for durability and reliability
- Brass valve bodies

Recommended Products/Accessories

- K-23723 Faucet cleaner

Warranty

See website for detailed warranty information.

KOHLER® One-Year Limited Warranty

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-08-2026 22:12 - US-CA

THE BOLD LOOK OF KOHLER.



Installation

- For 4" (102 mm) centers

Installation Notes

Install this product according to the installation instructions.

ADA compliant for handles only.
ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-08-2026 22:12 - US-CA

THE BOLD LOOK OF KOHLER.