KOHLER®

Persuade® | K-4326

Elongated toilet bowl with skirted trapway

Features

- Elongated bowl offers added room and comfort
- Comfort Height® feature offers chair-height seating that makes sitting down and standing up easier for most adults
- Skirted trapway simplifies cleaning
- Combines with the K-3569 or K-19042 tank to create a complete K-6355 or K-75790 Persuade toilet
- Standard 12" (305 mm) rough-in only. Cannot be combined with K-5383, or K-5381 for use in 10" or 14" installations
- Patented ReadyLock® installation system, a simple solution for skirted toilets, saves time, hassle, and eliminates the need to drill into the floor for standard 12" (305 mm) rough-in
- 2" (51 mm) glazed trapway

Available Colors/Finishes

Color tiles intended for reference only.

	0	White
	96	Biscuit
	NY	Dune
	95	Ice Grey
	7	Black Black

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-13-2026 20:00 - US-CA

THE BOLD LOOK OF KOHLER®

Codes/Standards

Accessibility standards may require controls to be located on the open side of the toilet.
Plumbing codes may require elongated toilets and elongated, open-front seats in public bathrooms.

ASME A112.19.2/CSA B45.1
ASME A112.19.14
DOE - Energy Policy Act 1992

Technical Information

Rough-in:	Standard 12" (305mm)
Flush Type:	Class Five
Bowl Shape:	Elongated
Seat-Mounting Holes:	5-1/2" (140 mm)
Waste Outlet:	Floor
Trapway Size:	2" (51 mm)
Trapway Type:	Skirted
Water Surface Size:	4-1/2" x 5-3/4" (114 mm x 146 mm)

Recommended Products/Accessories

- [object Object]23726 Drain treatment
- K-3569 Toilet tank, dual-flush
- K-19042 Toilet tank, dual-flush

Warranty

See website for detailed warranty information.

KOHLER® Toilets and Seats Limited Warranty

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-13-2026 20:00 - US-CA

THE BOLD LOOK OF KOHLER.

No image available.
This product is a component and not intended to be a standalone installation.

Installation

- Seat sold separately
- Standard 12" (305 mm) rough-in

Installation Notes

Install this product according to the installation instructions.

Product dimensions are nominal and may vary per ASME A112.19.2 tolerances.

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-13-2026 20:00 - US-CA

THE BOLD LOOK OF KOHLER.