


## ROUGHING-IN 尺寸图

Reference Value  
参考值

UNIT : mm  
单位: 毫米




K-702093T

K-702095T

Kohler reserves the right to change marked dimensions without prior notice.  
科勒公司保留随时变更图中标示尺寸的权利, 无需另行通知。


## INSTALLATION 安装

1. Confirm installation location. Clean floor and waste pipe.




1. 确定安装地漏的位置, 清理地面和排水管口。

2. Insert the floor outlet into the waste pipe and level the floor drain.




2. 将地漏排水口套进地面排水管内, 并调整地漏水平。

3. Move the floor drain away. Pour some mortar on the floor drain site. Apply some adhesive over the inside wall of the waste pipe.



3. 拿走地漏, 在预定位置倒上水泥砂浆, 并在排水管内壁涂上密封胶。


4. Insert the floor drain outlet back into the waste pipe and level the floor drain again.



4. 将地漏排水口套回地面排水管内, 并再次调整地漏水平。


KOHLER CHINA INVESTMENT CO., LTD NO.158, JIANG CHANG SAN ROAD,  
JING'AN DISTRICT, SHANGHAI, PRC POST CODE: 200436  
科勒(中国)投资有限公司 上海市静安区江场三路158号 邮编: 200436

5. After the adhesive cures, pour some water into the floor drain. Check for leakage.




5. 待密封胶凝固后，向地漏内倒水，检查是否有渗漏。

6. If there is no leakage, finish the following layer in proper order: mortar, primer coat, water-proof sealant, cement and tiles. The finished floor shall have a 2% slope.




6. 经测试无渗漏后，依次完成砂浆层，底漆层，防水层，水泥层和瓷砖层。完成后的瓷砖面应向地漏有2%的斜度。

7. Seal the gap between the floor drain and tiles with silicone. Put back the valve, strainer and grid.



7. 在地漏框同瓷砖的间隙内，打入硅胶，放入地漏芯，滤网和地漏盖板。

8. Insert wood board or ceramic tile into the floor drain assembly as desired.



8. 在地漏盖板组件中，客户根据自己的需要，在里面填充地板或瓷砖。

## CARE AND CLEANING

## 护理和清洁

For best results, keep the following in mind when caring for your KOHLER product:

为了长久使用，请在护理您的科勒产品时注意以下几点：

- Use a mild detergent such as liquid dishwashing soap and warm water for cleaning. Do not use abrasive cleaners that may scratch or dull the surface.
- Carefully read the cleaner product label to ensure the cleaner is safe for use on the material.
- Always test your cleaning solution on an inconspicuous area before applying to the entire surface.
- Do not allow cleaners to sit or soak on the surface.
- Wipe surfaces clean and rinse completely with water immediately after cleaner application. Rinse and dry any overspray that lands on nearby surfaces.
- Use a soft, dampened sponge or cloth. Never use an abrasive material such as a brush or scouring pad to clean surfaces.

- 使用中性清洁剂，例如液体洗洁精和温水进行清洗。请不要使用研磨清洁剂，以免刮划或使表面变钝。
- 请仔细阅读清洁剂说明以确认其更够在产品上安全使用。
- 在大面积使用清洁剂之前，请务必先在不显眼处先试验清洁方式。
- 请不要将产品表面浸泡在清洁剂中。
- 使用清洁剂后，请立即擦拭并用水彻底清洗。清洗并擦干溢溅在周围表面的清洁剂。
- 使用柔软湿润的海面或清洁布，请勿使用研磨材质，例如刷子和百洁布来清洁表面。