KOHLER®

Components® | K-77965

Bathroom sink faucet spout with Tube design, 1.2 gpm

Features

- Tall height is ideal for vessel-style sinks
- 1.2 gpm (4.5 lpm) maximum flow rate at 60 psi (4.14 bar)
- Laminar flow
- Includes metal touch-activated drain with 1-1/4" tailpiece
- Coordinate with your choice of Components bathroom sink faucet handles for a personalized design
- This product can help a building earn Water Efficiency points in LEED® Green Building Rating System

DISCONTINUED

Sustainability

WATER-SAVING DESIGN

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-12-2026 10:41 - US-CA

THE BOLD LOOK OF KOHLER®

Codes/Standards

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 372
NSF/ANSI/CAN 61
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)

Technical Information

All product dimensions are nominal.

Spout

Spout Reach: 6-11/16" (170 mm)

Flow Rate

Faucet Flow Rate: 1.2 gpm (4.5 l/min)

Valves

Required Valve: Thermostatic Mixer

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Recommended Products/Accessories

- [object Object]23726 Drain treatment
- K-78383 Vertical toilet paper holder
- K-78384 Covered double toilet paper holder
- K-23723 Faucet cleaner
- K-78372 18" towel bar
- K-78373 24" towel bar
- K-78375 Double towel bar
- K-78377 Towel arm
- K-78378 Robe hook
- K-78379 Double towel arm
- K-78382 Pivoting toilet paper holder

Required Products/Accessories

- K-77974-4 Lever bathroom sink faucet handles

or

- K-77974-8 Oyl bathroom sink faucet handles

or

- K-77974-9 Industrial bathroom sink faucet handles

or

- K-77963-8A Rocker bathroom sink faucet handle

Warranty

See website for detailed warranty information.

KOHLER® Faucet Lifetime Limited Warranty

DISCONTINUED

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-12-2026 10:41 - US-CA

THE BOLD LOOK OF KOHLER.



Installation

- Widespread or remote valve

Installation Notes

Install this product according to the installation instructions.

DISCONTINUED

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-12-2026 10:41 - US-CA

THE BOLD LOOK OF KOHLER.