Riverby® | K-8669-5UA3

33" undermount double-bowl workstation kitchen sink

Features

- 36" minimum base cabinet width
- Large/medium bowls
- 9" (229 mm) depth provides generous workspace
- Five oversized faucet holes
- Oversized holes allow for easy installation of faucets and accessories
- Bowl slopes toward drain to minimize water pooling
- Offset drains increase workspace in the sink and storage space underneath
- Includes K-6239 colander with integral cutting board, K-6194 utility rack with soaking cup, and K-9234 left-hand bottom sink rack

Sustainability

ENDURES FOR GENERATIONS

Available Colors/Finishes

Color tiles intended for reference only.

	0	White
	FF	Sea Salt
	96	Biscuit
	NY	Dune
	95	Ice Grey
	7	Black Black
	TRF	Truffle

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-18-2026 00:06 - US-CA

Codes/Standards

ASME A112.19.1/CSA B45.2

Technical Information

All product dimensions are nominal.

Number of Deck Holes:	5
Center(s):	8" (203 mm)
Drain Hole Diameter:	3-7/8" (98 mm)
Minimum Base Cabinet Width:	36" (914 mm)
Basin Configuration:	Large Bowl on Left
Left Basin Length:	17-9/16" (446 mm)
Left Basin Width:	15-13/16" (402 mm)
Left Basin Depth:	9" (229 mm)
Right Basin Length:	11-1/16" (281 mm)
Right Basin Width:	15-13/16" (402 mm)
Right Basin Depth:	9" (229 mm)

Material

- KOHLER® enameled cast iron

Included Components

- K-6239 Rinsing colander with cutting board (QTY 1)
- K-6194 Utility rack with soaking cup (QTY 1)
- K-9234 Sink rack (QTY 1)

Recommended Products/Accessories

- 1411886 Undermount Kit 23"
- [object Object]23726 Drain treatment
- K-23725 Cast iron cleaner
- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket, less tailpiece
- K-11352 Disposal flange with stopper
- K-9000 Adjustable P-trap with tubing outlet, 1-1/2" x 1-1/2"
- K-6255 Right-hand sink rack

Warranty

See website for detailed warranty information.

KOHLER® Enameled Cast Iron Kitchen and Bathroom Sink Lifetime Limited Warranty

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-18-2026 00:06 - US-CA

THE BOLD LOOK OF KOHLER.



Installation

- Undermount

Installation Notes

Install this product according to the installation instructions.

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-18-2026 00:06 - US-CA

THE BOLD LOOK OF KOHLER.