Archer® | K-9479

60" x 36" alcove shower base, center drain

Features

- Low-threshold design for easy entry and exit
- Covered drain with removable cover
- Single threshold for alcove installation
- Coordinates with other products in the Archer collection

Available Colors/Finishes

Color tiles intended for reference only.

	0	White
	96	Biscuit
	NY	Dune
	95	Ice Grey

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-12-2026 10:36 - US-CA

Codes/Standards

ASME A112.19.1/CSA B45.2
CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662

Technical Information

All product dimensions are nominal.

Drain Location:	Center
Drain Hole Diameter:	3-3/8" (86 mm)
Shower Ledge Minimum Flat:	2-5/8" (66 mm)
Minimum Floor Load:	17 lbs/ft²
Weight:	52 lbs (23.6 kg)

Material

- Acrylic

Recommended Products/Accessories

- [object Object]23726 Drain treatment
- K-23732 Tub & shower cleaner
- K-9132 Round shower drain for use with plastic pipe, gasket included
- K-706009-D3 56-5/8"-59-5/8" W x 74" H bypass shower door with 1/4"-thick Frosted glass
- K-706009-L 56-5/8"-59-5/8" W x 74" H bypass shower door with 1/4"-thick Crystal Clear glass
- K-706015-D3 56-5/8"-59-5/8" W x 74" H bypass shower door with 1/4"-thick Frosted glass
- K-706015-L 56-5/8"-59-5/8" W x 74" H bypass shower door with 1/4"-thick Crystal Clear glass

Warranty

See website for detailed warranty information.

KOHLER® Plastic Baths and Shower Bases Lifetime Limited Warranty

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-12-2026 10:36 - US-CA

THE BOLD LOOK OF KOHLER.



Installation

- Center drain

Installation Notes

Install this product according to the installation instructions.

Measure your actual product for rough-in details.
Shimming may be required to level the fixture.
Shimming may be required between the stud frame and the fixture.
Stud opening tolerance is + 1/4" (6 mm), - 0" (0 mm).

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-12-2026 10:36 - US-CA

THE BOLD LOOK OF KOHLER.