

DTV+™ | K-99696

Amplifier module

Features

- Audio amplifier with BLUETOOTH® wireless connectivity for streaming of audio input
- Reads your music or audio selections from any device enabled with BLUETOOTH® wireless technology
- Designed for use with the DTV+ digital system, but can also be used as a standalone amplifier enabled with BLUETOOTH® wireless technology
- Connects with up to four SoundTile® water-resistant speakers or any standard 4- or 8-ohm speakers (sold separately)
- Standby mode
- User definable device name and PIN code option when used with DTV+ digital system
- Two 1/7" (4 mm) input jacks for wired audio input
- One 1/7" (4 mm) line out jack
- Screw terminal block for two to four speakers
- One port for connection to DTV+ system controller
- One jack for power cord connection
- Syncs with devices enabled with BLUETOOTH® wireless technology including smartphones, MP3 players, tablets, and laptops located up to 33 feet (10 meters) away



Codes/Standards

None Applicable

Valves

Required Valve: Digital

Material

- Premium material construction for durability and reliability

Connectivity



The BLUETOOTH® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Kohler Co. is under license.

Required Electrical Service

One circuit required.

Amplifier Module: 1.2 A, 50/60 Hz

Electrical Component Ratings

Amplifier Module: 120/240 V, 1.2 A, 50/60 Hz


Power Cord Length: 6.0" (152 mm)

Warranty

See website for detailed warranty information.

KOHLER® Electronic Faucets, Valves, and Controls Five-Year Limited Warranty





Installation

- Supplied with rubber feet for locating on a countertop or shelf or can be wall mounted (mounting bracket and screws included)

Installation Notes

Install this product according to the installation instructions.

CAUTION: Risk of product damage. Do not install near heat sources (such as radiators or heat registers) or in any location where the temperature may exceed 104°F (40°C). This product is not water-resistant. Do not install in a location where excessive moisture, high humidity levels, or condensation are present.

Provide a minimum of 6" (152 mm) of space around the amplifier for proper air flow.

Provide unrestricted service access to the amplifier.

Locate the amplifier within close proximity to a 15 A 120 V electrical outlet. A GFCI outlet may be required in certain applications.

Amplifier allows 2-speaker or 4-speaker stereo output.

Determine the amplifier and speaker locations, allowing adequate reach for wires.



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

7-03-2026 10:04 - US-CA