



All-In-One 33" top-/undermount single-bowl kitchen sink kit K-R8437-2PC

Features

- Includes Malleco™ pull-down kitchen faucet with soap/lotion dispenser in Vibrant Stainless
- 1.8 gpm (6.8 lpm) maximum flow rate at 60 psi (4.14 bar)
- Faucet meets NSF 61 and NSF 372
- Includes top-filled soap/lotion dispenser
- One faucet hole with one accessory hole to the right
- 9-1/2" (241 mm) depth provides generous workspace
- Matte finish offers rich, dimensional color

Material

- KOHLER Neoroc® composite is durable and built to withstand day-to-day cleaning tasks
- Solid color throughout the sink
- Heat-resistant up to 750°F
- Scratch-, stain-, chip-, and thermal-shock-resistant

Installation

- Top-mount or undermount
- 36" minimum base cabinet width for undermount or top-mount installation

Recommended Products/Accessories

K-23726 Drain treatment
K-23730 Neoroc® cleaner

Optional Products/Accessories

K-11352 Disposal Flange with Stopper

Included Components

7400 Stainless Steel Sink Drain and Strainer
K-R562-SD Pull-down kitchen sink faucet with two-function sprayhead



Codes/Standards

ASME A112.18.1/CSA B125.1
CSA B45.5/IAPMO Z124
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
DOE - Energy Policy Act 1992
California Energy Commission (CEC)

KOHLER® Neoroc® Sinks Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.


| Color | Code | Description |
|-------|------|-------------|
|-------|------|-------------|



| | |
|-----|-------------|
| CM1 | Matte Black |
|-----|-------------|



All-In-One 33" top-/undermount single-bowl kitchen sink kit K-R8437-2PC



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 36" (914 mm)

Bowl area (Basin #1):
Length: 30-1/8" (765 mm)
Width: 16-15/16" (430 mm)
Bowl depth: 9-1/2" (241 mm)
Water depth: 9-1/2" (241 mm)

Number of deck holes: 1

Drain hole: 3-7/8" (98 mm)

Template: 1281757-7, required, included

Notes

Install this product according to the installation instructions.

NOTICE: Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 1-800-4-KOHLER). Kohler Co. is not responsible for cutout errors when the incorrect cut-out template is used.