

Features

- Vitreous china
- Undercounter
- With overflow
- Includes 52047 clamp assembly
- 530 x 365 x 206 mm [K-2214X]
- 581 x 402 x 206 mm [K-2215X]

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.1/CSA B45.1
- TIS 791-2544

Technical Information

Model	Drain hole	Water depth
K-2214X	44 mm D.	117 mm
K-2215X	44 mm D.	117 mm
Approximate measurements for comparison only.		

Included Components:	
Basin clamp assembly	52047
Cut-out template, K-2214X	1053195-X7
Cut-out template, K-2215X	1002977-X7



Specified Model

Model	Description	Color/Finished
K-2214X	Ladena 18" undercounter lavatory	0: White
K-2215X	Ladena 21" undercounter lavatory	0: White


Recommended Accessory		
K-8998	Adjustable P-trap	CP: Polished Chrome

Dimensions are approximate.

Unit: mm



UNDERCOUNTER LAVATORY K-2214X ALSO K-2215X




Installation Notes


Install this product according to instruction in the cut-out template. Supplied basin clamp assemblies require 25 mm minimum countertop thickness. Installer must supply anchors for thinner countertops.

NOTICE: Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 0-2204-6222) Kohler Co. is not responsible for cutout errors when the incorrect cut-out template is used.


Model	Dim	A	B	X	Y
K-2214X		474	310	530	365
K-2215X		524	347	581	402



Marble Installation



Wood Installation



Recommended ADA Installation

Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- สุขภัณฑ์เซรามิกประเภทวิทรีสไชน่า (Vitreous china)
- ติดตั้งแบบฝังใต้เคาน์เตอร์
- พร้อมม้วนน้ำล้น
- พร้อมชุดอุปกรณ์ยึดอ่างล้างหน้า รหัส 52047
- 530 x 365 x 206 มม. [K-2214X]
- 581 x 402 x 206 มม. [K-2215X]

มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- ASME A112.19.1/CSA B45.1
- มอก. 791-2544

ข้อมูลเฉพาะ

รุ่น	ขนาดรูสะดืออ่าง	ระยะน้ำลึก
K-2214X	เส้นผ่าศูนย์กลาง 44 มม.	117 มม.
K-2215X	เส้นผ่าศูนย์กลาง 44 มม.	117 มม.

*ระยะค่าโดยประมาณเพื่อการเปรียบเทียบเท่านั้น

ส่วนประกอบสุขภัณฑ์	
ชุดอุปกรณ์ยึดอ่างล้างหน้า	52047
กระดาดแม่แบบ, K-2214X	1053195-X7
กระดาดแม่แบบ, K-2215X	1002977-X7

รุ่นผลิตภัณฑ์



รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-2214X	อ่างล้างหน้าฝังใต้เคาน์เตอร์ ขนาด 18 นิ้ว รุ่น ลาเตน่า	0: สีขาว
K-2215X	อ่างล้างหน้าฝังใต้เคาน์เตอร์ ขนาด 21 นิ้ว รุ่น ลาเตน่า	0: สีขาว

อุปกรณ์แนะนำ

K-8998	ท่อน้ำทิ้งอ่างล้างหน้า	CP: สีโครมเงา
--------	------------------------	---------------

ขนาดระยะแสดงค่าโดยประมาณ


หน่วย: มม.



รุ่น	ระยะ	A	B	X	Y
K-2214X		474	310	530	365
K-2215X		524	347	581	402



การติดตั้งสำหรับเคาน์เตอร์หินอ่อน การติดตั้งสำหรับเคาน์เตอร์ไม้



การติดตั้งสำหรับผู้พิการ (ADA)

หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์

อ่างล้างหน้าฝังใต้เคาน์เตอร์ K-2214X และ K-2215X

