


Features

- Brass construction
- Single-hole mounting
- One-piece, self-contained ceramic disc joystick valve actuation allows both volume and temperature control
- Flexible connections for easy installation
- Touch-activated drain
- 135 mm spout reach
- Joystick lever handle

SINGLE-HOLE SINGLE CONTROL LAVATORY FAUCET K-16230X-4



Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2067-2552

Colors/Finishes

- CP: Polished Chrome

Accessories:

- CP: Polished Chrome

Specified Model

Model	Description	Color/Finished
K-16230X-4	Margaux single-hole single control lavatory faucet	CP

Product Specification:


The single-hole single control lavatory faucet shall be made of brass construction. Product shall feature a one-piece, self-contained ceramic disc valve, allowing volume and temperature control. Product shall be for single-hole mounting. Product shall feature a 135 mm spout reach, lever handle, a touch-activated drain, flexible connections for easy installation, and a joystick lever handle. Faucet shall be Kohler Model K-16230X-4-CP.

MARGAUX

Installation Notes

Install this product according to the installation guide.

Dimensions are approximate.
Unit: mm.



Product Diagram

คุณลักษณะ


- ผลิตจากทองเหลือง
- ติดตั้งแบบรูก๊อกเดี่ยว
- เซรามิคจอยสติ๊กวาล์ว วาล์วกักน้ำเดี่ยวควบคุมทั้งปริมาณน้ำและอุณหภูมิ
- ติดตั้งสายน้ำดี ทำให้ติดตั้งได้ง่าย
- พร้อมสະดืออ่างแบบกด
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 135 มม.
- มือบิดก้านโยกแบบจอยสติ๊ก

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2067-2552

ก๊อกผสมอ่างล้างหน้าแบบก้านโยก K-16230X-4



สี/วัสดุเคลือบผิว

- CP: สีโครมเงา

ส่วนประกอบอื่นๆ:

- CP: สีโครมเงา

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-16230X-4	ก๊อกผสมอ่างล้างหน้าแบบก้านโยก รุ่น มาร์คอก	CP

ข้อมูลผลิตภัณฑ์:


ก๊อกผสมอ่างล้างหน้าผลิตจากทองเหลือง วาล์วกักน้ำเป็นเซรามิควาล์ว ก๊อกน้ำวาล์วเดี่ยวที่ควบคุมทั้งปริมาณน้ำและอุณหภูมิ ก๊อกน้ำติดตั้งแบบรูก๊อกเดี่ยว มีระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 135 มม. ติดตั้งด้วยสายน้ำดีทำให้ติดตั้งได้ง่าย ก๊อกน้ำแบบก้านโยกจอยสติ๊กพร้อมสະดืออ่างแบบกด ก๊อกน้ำรุ่นนี้คือ ก๊อกน้ำโคห์เลอร์รุ่น K-16230X-4-CP

มาร์กอส

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.



ภาพแสดงผลิตภัณฑ์