

KITCHEN SINK K-3369X

Features

- 304 stainless steel
- Self-rimming
- Double basin
- Includes flexible trap, overflow trap, quick flow strainer, soap dispenser, colander and installation hardware
- Exceptional sound-absorption technology (SilentShield technology)
- 790 x 480 x 208 mm


Codes/Standards Applicable

Specified model meets or exceeds the following:

- GB/T 18884.2-2002

Installation Notes

Install this product according to the installation guide. Allow a minimum of 2" (51 mm) clearance around the sink rim for clip attachment.



Technical Information


Fixture:	Left bowl	Right bowl
Basin area	344 x 370 mm	344 x 370 mm
Water depth	198 mm	198 mm
Drain hole	ø90 mm	
Faucet hole	ø35 mm	
*Approximate measurements for comparison only.		

Included components:	
Flexible trap	SP1200369
Strainer	SP1174273, SP1141126
Fixing clips	SP1071179
Soap dispenser	78289X-NA
Colander	3368X-NA
Template	1111246-X7

Specified Model

Model	Description	Color/Finished
K-3369X-2KD	Staccato stainless steel sink	NA: None Applicable
Recommended Accessories		
K-12177X	Fairfax kitchen faucet	CP: Polished Chrome

Dimensions are approximate.
Unit: mm



Product Diagram

คุณลักษณะ


- ผลิตจากสแตนเลส สเต็ล เกรด 304
- แบบฝังบนเคาน์เตอร์
- สองหลุม
- พร้อมข้อต่อน้ำทิ้ง, ท่อน้ำล้น, สะตืออ่างแบบควิกโฟว์, ที่ใส่น้ำยาล้างจาน, ตะกร้าใส่ผัก และอุปกรณ์ติดตั้ง
- เทคโนโลยีไฮเลนซิลด์ ช่วยลดการเกิดเสียงจากงานขามู, ลดการเกาะตัวของหยดน้ำ และช่วยรักษาอุณหภูมิของน้ำ
- 790 x 480 x 208 มม.

มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- GB/T 18884.2-2002

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง
 เมื่อพื้นที่วางรอบขอบอ่างล้างจานไว้อย่างน้อย 2 นิ้ว (51 มม.)
 สำหรับการติดตั้งอุปกรณ์ยึดอ่างล้างจานที่มาพร้อมกับผลิตภัณฑ์



ข้อมูลเฉพาะ


ผลิตภัณฑ์:	หลุมซ้าย	หลุมขวา
พื้นที่อ่าง	344 x 370 มม.	344 x 370 มม.
ระยะน้ำล้น	198 มม.	198 มม.
ขนาดรูท่อน้ำทิ้ง	Ø90 มม.	
ขนาดรูท่อน้ำ	Ø35 มม.	
*ระยะค่าโดยประมาณเพื่อเปรียบเทียบเท่านั้น		

ส่วนประกอบผลิตภัณฑ์	
ข้อต่อท่อน้ำทิ้ง	SP1200369
สะตืออ่าง	SP1174273, SP1141126
อุปกรณ์ติดตั้ง	SP1071179
ที่ใส่น้ำยาล้างจาน	78289X-NA
ตะกร้าใส่ผัก	3368X-NA
กระดาดแม่แบบ	1111246-X7

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-3369X-2KD	อ่างล้างจานสแตนเลส สองหลุม รุ่นสตักคาโต้	NA: สีสตาม์วัสดุ
อุปกรณ์แนะนำ		
K-12177X	ก๊อกลงอ่างล้างจาน รุ่นแฟร์แพกซ์	CP: สีโครมเงา

ขนาดระยะแสดงค่าโดยประมาณ
 หน่วย: มม.



ภาพแสดงผลิตภัณฑ์