

KITCHEN SINK K-3664X

Features

- 304 stainless steel
- Self-rimming and undercounter
- Large and medium basin
- Includes flexible trap, overflow trap, quick flow strainer, colander and installation hardware
- Exceptional sound-absorption technology (SilentShield technology)
- 840 x 440 x 213 mm


Codes/Standards Applicable

Specified model meets or exceeds the following:

- GB/T 18884.2-2002

Installation Notes

Install this product according to the installation guide. Allow a minimum of 2" (51 mm) clearance around the sink rim for clip attachment.



Technical Information


Fixture:	Left bowl	Right bowl
Basin area	313 x 373 mm	437 x 373 mm
Water depth	135 mm	180 mm
Drain hole	ø90 mm	
*Approximate measurements for comparison only.		

Included components:	
Flexible trap	SP1200369
Strainer	5163X-NA, SP1141126
Fixing clips	SP1071179, SP1127254
Colander	SP1097100
Template	1104367-X7

Specified Model

Model	Description	Color/Finished
K-3664X-F	Prologue stainless steel sink	NA: None Applicable
Recommended Accessories		
K-15609X-4	Elate kitchen faucet	CP: Polished Chrome

Dimensions are approximate.
Unit: mm



Product Diagram

อ่างล้างจาน K-3664X

คุณลักษณะ


- ผลิตจากสแตนเลส สตีล เกรด 304
- แบบฝังบนเคาน์เตอร์และฝังใต้เคาน์เตอร์
- หนึ่งหลุมครึ่ง
- พร้อมข้อต่อน้ำทิ้ง, ท่อน้ำล้น, สะตืออ่างแบบควิกไฟว์, ตะกร้าใส่ผัก และอุปกรณ์ติดตั้ง
- เทคโนโลยีไฮเดนซิดด์ ช่วยลดการเกิดเสียงจากจานชาม, ลดการเกาะตัวของหยดน้ำ และช่วยรักษาอุณหภูมิของน้ำ
- 840 x 440 x 213 มม.

มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- GB/T 18884.2-2002

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง
 เมื่อพื้นที่วางรอบขอบอ่างล้างจานไว้อย่างน้อย 2 นิ้ว (51 มม.)
 สำหรับการติดตั้งอุปกรณ์ยึดอ่างล้างจานที่มาพร้อมกับผลิตภัณฑ์



ข้อมูลเฉพาะ


ผลิตภัณฑ์:	หลุมซ้าย	หลุมขวา
พื้นที่อ่าง	313 x 373 มม.	437 x 373 มม.
ระยะน้ำล้น	135 มม.	180 มม.
ขนาดรูท่อน้ำทิ้ง	Ø90 มม.	
*ระยะค่าโดยประมาณเพื่อเปรียบเทียบเท่านั้น		

ส่วนประกอบผลิตภัณฑ์	
ข้อต่อท่อน้ำทิ้ง	SP1200369
สะตืออ่าง	5163X-NA, SP1141126
อุปกรณ์ติดตั้ง	SP1071179, SP1127254
ตะกร้าใส่ผัก	SP1097100
กระดาษแม่แบบ	1104367-X7

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-3664X-F	อ่างล้างจานสแตนเลส หนึ่งหลุมครึ่ง รุ่นโปรล็อก	NA: สีตามวัสดุ
อุปกรณ์แนะนำ		
K-15609X-4	ก๊อกลบอ่างล้างจาน รุ่นอีเลท	CP: สีโครมเงา

ขนาดระยะแสดงค่าโดยประมาณ
 หน่วย: มม.



ภาพแสดงผลิตภัณฑ์