

KITCHEN SINK K-3710X


Features

- 304 stainless steel
- Self-rimming
- Double (equal) compartment
- Includes S-trap, overflow trap, quick flow strainers, installation hardware, soap dispenser, cutting board, and wire colander
- Exceptional sound-absorption technology (SilentShield technology)
- 820 x 500 x 207 mm

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI A112.19.3M/CSA B45.4
- QB/T 4013



Technical Information

Fixture:	Left	Right
Basin area	315 x 385 mm	305 x 315 mm
Water depth	165 mm	135 mm
Drain hole	38 or 51 mm (1-1/2" or 2")	
Faucet hole	35 mm	

*Approximate measurements for comparison only.

Included components:	
S-trap	SP1200369
Strainer	5163X-NA/SP1174273
Fixing clips	SP1071179
Soap dispenser	78289X-NA
Cutting board	SP1104805
Wire colander assy	SP1119053
Template	1131759-X7


Installation Notes

Install this product according to the installation guide. Allow a minimum of 2" (51 mm) clearance around the sink rim for clip attachment.

Specified Model

Model	Description	Color/Finished
K-3710X-2FD	Linc self-rimming kitchen sink	NA: None Applicable
Recommended Accessories		
K-6332T-4	Evoke kitchen faucet	CP: Polished Chrome

Dimensions are approximate.
Unit: mm



Product Diagram

คุณลักษณะ


- ผลิตจากสแตนเลส 304 เกรด 304
- แบบฝังบนเคาน์เตอร์
- สองหลุม
- พร้อมข้อต่อน้ำทิ้งแบบลงพื้น, ท่อน้ำล้นในตัว, สะดืออ่างแบบควิกไฟร์, อุปกรณ์ติดตั้ง, ที่ใสน้ำยาล้างจาน, เชียงไม้ และตะกร้า
- เทคโนโลยีไฮเลนซิลด์ ช่วยลดการเกิดเสียงจากจานชาม, ลดการเกาะตัวของหยดน้ำ และช่วยรักษาอุณหภูมิของน้ำ
- 820 x 500 x 207 มม.

มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- ANSI A112.19.3M/CSA B45.4
- QB/T 4013

อ่างล้างจาน

K-3710X



ข้อมูลเฉพาะ

ผลิตภัณฑ์:	ซ้าย	ขวา
พื้นที่อ่าง	315 x 385 มม.	305 x 315 มม.
ระยะน้ำลึก	165 มม.	135 มม.
ขนาดรูท่อน้ำทิ้ง	38 หรือ 51 มม. (1-1/2" หรือ 2")	
ขนาดรูท่อน้ำ	35 มม.	

*ระยะค่าโดยประมาณเพื่อเปรียบเทียบเท่านั้น

ส่วนประกอบผลิตภัณฑ์	
ข้อต่อท่อน้ำทิ้งแบบลงพื้น	SP1200369
สะดืออ่าง	5163X-NA/SP1174273
อุปกรณ์ติดตั้ง	SP1071179
ที่ใสน้ำยาล้างจาน	78289X-NA
เชียงไม้	SP1104805
ตะกร้า	SP1119053
กระดาษแม่แบบ	1131759-X7

ข้อสังเกตสำหรับการติดตั้ง


ติดตั้งผลิตภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง
 เพื่อพื้นที่ว่างรอบขอบอ่างล้างจานไว้อย่างน้อย 2 ซิน (51 มม.)
 สำหรับการติดตั้งอุปกรณ์ยึดอ่างล้างจานที่มาพร้อมกับผลิตภัณฑ์

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-3710X-2FD	อ่างล้างจาน สองหลุม รุ่นลินซ์	NA: สีตามวัสดุ
แนะนำให้ใช้ร่วมกับผลิตภัณฑ์		
K-6332T-4	ก๊อกลสมอ่างล้างจานชนิดฝักบัว รุ่นอีโวก	CP: สีโครมเงา

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



ภาพแสดงผลิตภัณฑ์