

**Carburetor Heater Kits**

GM19462-KP4-QS



GM57969-KP5-QS

**Note:** 120 volt kits shown.

**Applicable Models**

- 6VSG
- 8/10/12RESV/RESVL
- 8.5RES
- 12RES/RESL
- 14RESA/RESAL
- 14RCA/RCAL
- 20RESA/RESAL
- 20RESB
- 20RESC/RESCL
- 20RESD
- 20RCA/RCAL
- 26RCA/RCAL

**Description**

Carburetor heater kits are recommended for improved cold starting in locations where the temperatures falls below 0°C (32°F). Carburetor heaters prevent condensation and carburetor icing. The heater turns on when the temperature at the thermostat falls below approximately 4°C (40°F) and turns off when the temperature rises above approximately 16°C (60°F).

The carburetor heater for models 6VSG, 8.5RES, 12RES/RESL, 14RESA/RESAL and 14RCA/RCAL mounts between the engine air cleaner and the carburetor. The carburetor heater for models 8/10/12RESV/RESVL uses an adaptor (included) to mount on the carburetor. The carburetor heater for models 20RESA/RESAL, 20RCA/RCAL, 26RCA/RCAL, 20RESB, 20RESC/RESCL, and 20RESD fits into a threaded opening on the carburetor.

Carburetor heater kits are available in 120 volt or 240 volt versions.

**Note:** The heater requires a continuous source of AC power that is backed up by the generator set.

**Note:** See page 2 or the Kohler Price List for kit selection by generator set model.



## Carburetor Heater Specifications

Kits	GM19462-KP3-QS	GM19462-KP4-QS	GM57969-KP3-QS	GM57969-KP5-QS
Heater rating	240 VAC, 37 W	120 VAC, 37 W	240 VAC, 37 W	120 VAC, 37 W
Thermostat ON	4 ± 3°C (40 ± 5°F)		4 ± 4°C (40 ± 7°F)	
Thermostat OFF	16 ± 3°C (60 ± 5°F)		16 ± 3°C (60 ± 5°F)	
Cord length	1905 mm (75 in.)		382 mm (15 in.)	

## Kit Contents

Kits	GM19462-KP3-QS	GM19462-KP4-QS
Voltage	240 VAC	120 VAC
Description	Qty.	Qty.
Bushing	1	1
Cable tie	2	2
Cord, 3-way extension	—	1
Decal	1	1
Heater, carburetor	1	1
Installation Instructions	1	1
Insulator, breather line	1	1
Plug, button	1	1
Screw	4	4
Tube, breather	1	1

Kits	GM57969-KP3-QS	GM57969-KP5-QS
Voltage	240 VAC	120 VAC
Description	Qty.	Qty.
Adapter	—	1
Bushing	2	—
Cord, 3-way extension	—	1
Decal	1	1
Heater, carburetor	1	1
Installation Instructions	1	1

## Generator Models and Kits

Kit Number (VAC)	Generator Models
GM19462-KP3-QS (240VAC)	14RESA
GM19462-KP4-QS (120VAC)	6VSG 8.5RES 12RES/RESL 14RESA/RESAL 14RCA/RCAL
GM57969-KP3-QS (240VAC)	20RESA 20RESB 20RESC 20RESD 20RCA
GM57969-KP5-QS (120VAC)	8/10/12RESV/RESVL 20RESA/RESAL 20RESB 20RESC/RESCL 20RESD 20RCA/RCAL 26RCA/RCAL

**DISTRIBUTED BY:**

Availability is subject to change without notice. Kohler Co. reserves the right to change the design or specifications without notice and without any obligation or liability whatsoever. Contact your local Kohler® generator distributor for availability.

© 2013 Kohler Co. All rights reserved.