

SELF-RIMMING LAVATORY K-2196X


Features

- Vitreous china
- Self-rimming
- With overflow
- Available in single-hole or 8" centers
- 514 x 445 x 215 mm

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2/CSA B45.1
- TIS 791-2544



Technical Information

Fixture:	
Water depth	129 mm
Drain hole	44 mm D.
*Approximate measurements for comparison only.	
Included Components:	
Cut-out template	1002970-X7

Installation Notes

Install this product according to instruction in the cut-out template.


NOTICE: Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 0-2204-6222) Kohler Co. is not responsible for cutout errors when the incorrect cut-out template is used.

Specified Model

Model	Description	Color/Finished
K-2196X-1	Pennington self-rimming lavatory, single-hole	0: White
K-2196X-8	Pennington self-rimming lavatory, 8" centers	0: White

Recommended Accessory		
K-8998	P-trap	CP: Polished Chrome

Dimensions are approximate.
Unit: mm




Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

อ่างล้างหน้าฝึงบนเคาน์เตอร์

K-2196X



คุณลักษณะ

- สุขภัณฑ์เซรามิกประเภทวิเทรียสไชน่า (Vitreous china)
- ติดตั้งแบบฝึงบนเคาน์เตอร์
- พร้อมรูน้ำล้น
- แบบเจาะรูเดี่ยว หรือแบบเซ็นเตอร์ 8"
- 514 x 445 x 215 มม.

มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- ASME A112.19.2/CSA B45.1
- มอก. 791-2544

ข้อมูลเฉพาะ

สุขภัณฑ์	
ระยะน้ำลึก	129 มม.
ขนาดรูสะดืออ่าง	เส้นผ่าศูนย์กลาง 44 มม.
*ระยะค่าโดยประมาณเพื่อการเปรียบเทียบเท่านั้น	
ส่วนประกอบสุขภัณฑ์	
กระดาดแม่แบบ	1002970-X7

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์ตามคำแนะนำในกระดาดแม่แบบ

ข้อพึงระวัง: การตัดรูเจาะเคาน์เตอร์ต้องใช้กระดาดแม่แบบที่อยู่ในชุดผลิตภัณฑ์ หรือได้รับจากบริษัทโคห์เลอร์ฯ เท่านั้น (โทร. 0-2204-6222) บริษัทฯ จะไม่รับผิดชอบการตัดเคาน์เตอร์ที่เกิดจากการผิดพลาดหากใช้กระดาดแม่แบบที่ไม่ถูกต้อง

รุ่นผลิตภัณฑ์



รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-2196X-1	อ่างล้างหน้าฝึงบนเคาน์เตอร์ แบบเจาะรูเดี่ยว รุ่น เพนนิ่งตัน	0: สีขาว
K-2196X-8	อ่างล้างหน้าฝึงบนเคาน์เตอร์ แบบเซ็นเตอร์ 8" รุ่น เพนนิ่งตัน	0: สีขาว

อุปกรณ์แนะนำ

K-8998	ท่อน้ำทิ้งอ่างล้างหน้า	CP: สีโครมเงา
--------	------------------------	---------------

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์